




FEATURES:

- Converts a Female Phono (RCA) Jack to a BNC Male
- Converts a BNC Female Jack into a Phono (RCA) Plug
- Lengths other than those specified are available on request.

MATERIALS:

Conn: 1st End-Phono Plug

Material: Body and Center Contact – Brass.

Finish: Body and Center Contact – Nickel plated.

Strain Relief Boot: PVC molded to Phono plug and cable.

Color: Black.

Cable: Coaxial, RG 59B/U.

Impedance: 75 Ohms 6.15 (.242) O.D.

Marking: "POMONA 4963-E-XX".

Conn: 2nd End-BNC Male

Finish: Body and fittings – Tarnish resistant.

Center Contact – Gold plated per

MIL-C-39012.

Strain Relief Boot: PVC molded to BNC plug and cable.

Color: Black.

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 500 VRMS/DC

ORDERING INFORMATION: Model 4963-E-XX

XX=Cable length, Standard Lengths: 24" (610), 36" (914), 48" (1219), 60" (1524)

Ordering Example: 4963-E-60 indicates 60" in length

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA