

United States > Products & Services > Electronics, Electrical, and Communications > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Terminals, Kits and Tools > Terminals > 3M™ Scotchlok™ Ring Tongues > 3M™ Scotchlok™ Ring Nylon Insulated, 10/bottle, MN4-38RX

Find An Account Rep


Where To Buy (Find A Distributor)

Contact Us

3M™ Scotchlok™ Ring Nylon Insulated, 10/bottle, MN4-38RX

UPC # 000511285900273M Product Number MN4-38RX3M ID 80611466485

PrintShare



Ring Nylon Insulated, 10/bottle, MN4-38RX

X

Network Access Message: The page cannot be displayed.






Need Help?

Questions? We can help

Contact Us

Overview	Support
Specifications	
Agency Approvals	UL and CSA
Barrel Inside Diameter	0.28 Inch
Barrel Length	0.47 Inch
Barrel Style	Brazed
Brand	Scotchlok
China RoHS - Below MCV	No
Clearance (C)	0.53 Inch
Conductor Sizes	4 AWG
CSA File Number	LR22190
Dimension E	1.41 Inch
EU RoHS Compliant	Yes
Insulation Material	Nylon
Length (L)	1.74 Inch
Maximum Insulation Outer Diameter	0.515 Inch
Packaging	10 per bottle
Stud Size	3/8 Inch
Terminal Style	Standard
Terminal Type	Ring
Thickness	0.075 Inch
UL File Number	E23438
Width (W)	0.68 Inch

People who viewed this item also viewed

 Disj				 Disj
3M™ Scotchlok™ Ring Vinyl Insulated, 50/bottle, MVU10-14R/SX	3M™ Scotchlok™ Ring Tongue Nylon Insulated Brazed Seam MN4-516RK, Stud Size 5/16	3M™ Scotchlok™ Ring Vinyl Insulated, 50/bottle, MVU10-6RX	3M™ Scotchlok™ Ring Nylon Insulated, 50/bottle, MNG10-14R/SX	3M™ Scotchlok™ Ring Nylon Insulated, 50/bottle, MNG10-6RX