



Representative

Catalog Number: 304
Product ID: 7TAA106020R0000
UPC Number: 78621000304
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.906 to 1.093 Inch, Malleable Iron with Zinc Plating

- For use with Armored Cable and Flexible Metal Conduit

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E1383, CSA
Size	3/4 Inch
Conductor Range	0.906 to 1.093 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	23.02mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x5x8
Outer Quantity	100
Outer Dimensions (inches)	10.5x8.7x8.8
Weight Uom	16.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com