


Jumper 2,54 mm

Series

149



Rated current	3,0 A
Material contact	Phosphor bronze
Plating contact	Sn, Au
Colour	Black, Red, Green, Blue, Yellow, Grey, White
Material insulator	Thermoplast UL94V-0
Operating temperature	-40°C to +105°C

pitch
2,54


mating pin
size
□ 0,64

max.
pincount
002

All dimensions in mm.


Variation

Open top




1

Closed top




2

Open top, short



3

Closed top with handle



4

Plating:
T = Sn
F = Au

Colour:
0 = Black
1 = Red
2 = Green
3 = Blue
4 = Yellow
5 = Grey
6 = White

Variation (1,2,3,4)

No. of contacts

Plating contact (T,F)
Colour (0,1,2,...)



www.mpe-connector.de

Order code:

149-?-002-??-XS

Mating series
see page

087 089 090 585 088 334 368 296
3-37 3-38 3-39 3-40 3-41 3-42 3-43 3-53