




Isolierkörpermaterial
PBT, UL94V-0

Kontaktmaterial
Phosphorbronze

Kontaktoberfläche
Ni, Sn

Kontaktwiderstand
20mΩ max

Isolationswiderstand
5000MΩ min

Strombelastbarkeit
1A

Betriebstemperatur
-25°C - +85°C

Betriebsspannung
60V AC

Prüfspannung
1000V AC

Verpackung
Stangenverpackung

Insulator material
PBT, UL94V-0

Contact material
Phosphor bronze

Plating
Ni, Sn

Contact resistance
20mΩ max

Insulation resistance
5000MΩ min

Current rating
1A



Operating temperature
-25°C - +85°C

Operating voltage
60V AC

Test voltage
1000V AC

Packing
Tube packing

Dimensions			
No. of contacts	A	B	C
06	7.62	10.16	7.62
08	10.16	10.16	7.62
14	17.78	10.16	7.62
16	20.32	10.16	7.62
18	22.86	10.16	7.62
20	25.40	10.16	7.62
24*	30.48	17.78	15.24
24	30.48	10.16	7.62
28	35.56	17.78	15.24
28*	35.56	10.16	7.62
32	40.64	17.78	15.24
40	50.80	17.78	15.24



Bestellcode / Ordercode

Polzahl

06 / 08 / 14 / 16 / 18 / 20 /
24 / 28 / 32 / 40

No. of contacts

06 / 08 / 14 / 16 / 18 / 20 /
24 / 28 / 32 / 40

Ausführung

-TT - Standard
/7-T - Raster 2.54 x 7.62*
(nur 24 und 28polig)

Version

-TT - Standard
/7-T - Pitch 2.54 x 7.62*
(only 24 and 28poles)

A **xx** - **LC** **x**

Bitte „x“ durch die geeignete Option ersetzen
Please replace „x“ appropriate option