


## Dimensions: mm (In.)



POS.1	POS.2	POS.3
ON	OFF	ON
2-3		2-1
	OPEN	

SWITCH FUNCTION

**Mechanical Specifications:**

- Operating Temperature: -30° C to +85° C.

**Mechanical Specifications:**

- Electrical Life: 40,000 make-and-break cycles at full load
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Rating: 2A/250VAC, 5A/120VAC or 28 VDC
- Dielectric Strength: 1,000 V RMS@ sea level.

**Materials:**

- Case: Diallyl phthalate (DAP)
- Acutuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Terminal/Contact: Silver or Gold plated.

**Note:**

- RoHS compliant by exemption

Toggle Switch  
108-1MS3T2B3M1QE-EVX

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com)

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-1MS3T2B3M1QE-EVX](#)