



Home> Products > Light Curtains> FF-SNC> Product Page

FF-SNC1SA05PA-QD



Actual product appearance may vary.

FF-SNC sensor/actuator pair, ABS housing, 5 m [16.40 ft] cordset (included)

Supporting Documentation

-  [Dimensions](#)
-  [Installation Instructions and Approvals Documentation](#)
-  [Wiring Diagram](#)

Product Specifications	
Product Type	FF- SNC sensor/actuator pair, ABS housing, 5 m [16.40 ft] cordset (included)
Safety Type/Category	1,2,3
Scanning Range	ON: 5 to 7 mm [0.20 to 0.27 in], OFF: 8 to 12 mm [0.32 to 0.47 in]
Housing Size	28 mm H x 52 mm W x 14 mm D [1.10 in H x 2.04 in W x 0.55 in D]
Connector Type	M8 Connector, 5 m [16.40 ft] cordset (included)
Approvals	TUV,cULus,CE
Availability	Global
Temperature	- 10 °C to 55 °C [14 °F to 131 °F]
Sealing	IP67
UNSPSC Code	30211930
UNSPSC Commodity	30211930 Photoelectric sensors
Series Name	FF- SNC
Used with	FF- SNC control and extension units
Listing Used with	FF- SNC200R2, FF - SNC400R2, FF - SNC400R2, FF - SNC1EXT

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search