




GUARDIAN
Electric Manufacturing

ISO 9001 / AS9100 Certified Company

Woodstock, IL 60098 Ph. (815)334-3600 Fax (815)337-0377

Or visit us at our website www.guardian-electric.com

Model TP12 x 13 Push-Type DC Tubular Solenoid



Solenoid shown energized and fully seated.

Supplied with mounting bracket, hex nut and lockwasher (not shown).

Spring kits are available (consult factory).

Total Weight: 10.2 oz.

Plunger Weight: 1.65 oz.

Model No.	Part No.	Duty Cycle	Voltage	Resistance (Ω)	Power (W)	Current
TP12x13-I-12	A422-064103-03	Intermittent	12VDC	7.3	20.7	1.64 A
TP12x13-C-12	A422-064103-04	Continuous	12VDC	22.8	6.6	526 mA
TP12x13-I-24	A422-064103-01	Intermittent	24VDC	28.4	21.3	845 mA
TP12x13-C-24	A422-064103-02	Continuous	24VDC	90.4	6.7	265 mA

When ordering, please refer to Part No., as listed above.

Consult factory for custom configurations.

Push Force (oz.)									Holding Force (oz.)
Stroke (in.)	0.050	0.125	0.250	0.375	0.500	0.625	0.750	1.000	-
Continuous Duty	64	32	20	15	4	2	1	n/a	146
Intermittent Duty	112	84	44	28	16	12	5	n/a	168

UL Recognition

Recognized under the 
Component Recognition Program of
Underwriters Laboratories, Inc.

Continuous Duty

100% 'On' Time

Intermittent Duty

25% 'On' Time, (100 Seconds 'On' Max.
Followed By 300 Seconds 'Off' Min.)

RoHS

These parts comply with **RoHS** Directive 2002/95/EC