

modular sealed enclosures SE

technical characteristics

- Sealing: IP 55.
- Two offers available:
 - enclosures with knock-out entries,
 - enclosures with smooth faces.
- Two versions:
 - enclosures in polycarbonate,
 - enclosures in polystyrene.
- Resistance to external mechanical impact:
 - IK 08, for the polycarbonate versions,
 - IK 07, for the polystyrene versions.
- Non flame propagating insulating material.
- Colour grey RAL 7035.

installation

- Transparent and sealed hinged inspection cover.
- Support for terminal blocks (12 x 2, flat).
- For units with maximum shoulder height of 52 mm.
- Shutters and double insulation caps included with enclosure.

advantages

- Transparent inspection cover:
 - clear on polycarbonate enclosures,
 - smoked on polystyrene enclosures.
- 3 and 4 module enclosures are the smallest available on the market.



references

enclosures SE references			no. of modules
with knock-out entries		with smooth faces	
polycarbonate	polystyrene	polycarbonate	
ENN80903	ENN80603	ENN80930	3
ENN80904	ENN80604	ENN80934	4
ENN80906	ENN80606	ENN80936	6
ENN80910	ENN80610	ENN80940	10
ENN80911	ENN80611	—	10
ENN80913	ENN80613	—	13
ENN80914	ENN80614	—	13
ENN80916	ENN80616	—	16
ENN80926	ENN80626	—	26

characteristics of enclosures with knock-out entries

reference polycarbonate IP 55	reference polystyrene IP 55	number of stepped entries			number of knock-out entries		
		Ø 20	Ø 25	Ø 32	Pg 16	Pg 21	Pg 29
ENN80903 (1) (2)	ENN80603 (1) (2)	2	—	—	—	—	—
ENN80904	ENN80604	2	1	—	—	—	—
ENN80906	ENN80606	3	1	—	2	—	—
ENN80910	ENN80610	—	5	1	—	2	—
ENN80911	ENN80611	—	5	1	—	2	—
ENN80913 (3)	ENN80613 (3)	—	5	1	—	2	—
ENN80914	ENN80614	—	4	1	—	1	1
ENN80916	ENN80616	—	6	1	—	2	1
ENN80926	ENN80626	—	5	1	—	2	—

(1) Sealable with plug ref. ENN09140.

(2) Without terminal support. 45 mm maximum shoulder height of units.

(3) Inspection cover not sealable.

modular sealed enclosures SE

accessories

- Ø 8 mm sealing plugs for enclosure ref. ENN80903.
- Set of 4 wall fixing lugs for all enclosure models.
- Snap-off shutters, strip of 4 + 2 half-modules.





Terminal strips

page 527

reference	description
ENN09140	Sealing plugs
ENN09106	Wall fixing lugs
ENN80305	Shutters

dimensions



version reference		dimensions			fixings							number of modules Z
					external to enclosure	internal to enclosure	F	G	H	H'	J	
polycarbonate	polystyrene	A	B	C	D	E	F	G	H	H'	J	Z
ENN80903	ENN80603/ENN80930	135	74	97	—	—	95	50	47	—	26.5	3
ENN80904	ENN80604/ENN80934	170	105	111	153	88	122	53	52	46	37	4
ENN80906	ENN80606/ENN80936	170	135	112	—	—	130	80	51	45	39	6
ENN80910	ENN80610/ENN80940	168	220	112.5	151	203	130	180	51	45	39	10
ENN80911	ENN80611	270	220	120	240	190	201	190	58.5	47.5	39	10
ENN80913	ENN80613	340	270	119.5	314	244	280	210	56.5	45.5	36	13
ENN80914	ENN80614	220	270	120	190	240	190	201	58.5	47.5	39	13
ENN80916	ENN80616	270	340	138	244	314	210	280	56.5	45.5	36	16
ENN80926	ENN80626	340	270	119.5	314	244	280	210	56.5	45.5	36	26 (2 x 13)
ENN80232	—	375	325	135	—	—	340	190	51	44	46	32 (2 x 16)