

# PRODUCT SPECIFICATION

|                         |                                                                                                                                                                       |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Brand</b>            | Jokari                                                                                                                                                                |
| <b>Product Range</b>    | Cable/Wire strippers                                                                                                                                                  |
| <b>Catalogue number</b> | 10160, 10270, 10271, 10280, 10282,<br>10283, 20030, 20050, 20060, 20090,<br>20100, 20300, 20310, 20450, 30010,<br>30100, 30120, 30140, 30155, 30160,<br>30400, 30600, |
| <b>Date</b>             | 16/05/2014                                                                                                                                                            |

## Range Description

Jokari Cable/Wire strippers

## Features

### 10160 & 10270

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Spare cutting blade in the handle.
- 10160 - Working Range 4 - 16 mm Ø
- 10270 - Working Range 8 - 28 mm Ø

### 10271

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Spare cutting blade in the handle
- Working Range 8 – 28 mm Ø

### 10280

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Additional external hook & straight blade for convenience
- Spare cutting blade in the handle
- Cable Knife with Soft Grip
- Working Range 8 - 28 mm Ø



10160/10270



10271



10280

### 10282

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping of round cables
- Suitable for round multicore cables for fixed installation, Flexible cables, Damp-proof installation cables e.g NYM, NYY
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Knives Titanium-Nitride coated (TIN) for a longer life, faster cutting and less wear.
- With TIN coated hooked blade and protection cap.
- Including TIN coated spare blade in the handle.
- Working Range 8 - 28 mm Ø



10282

### 10283

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Additional external hook & straight blade for convenience
- Spare cutting blade in the handle
- Working Range 8 - 28 mm Ø



10283

### 10350

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Spare cutting blade in the handle.
- Dual compound handle for better grip and safety.
- Suitable for stripping round multicore cables of 27-35mm Ø



10350

### 10500

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Spare cutting blade in the handle.
- Dual compound handle for better grip and safety.
- Suitable for stripping round multicore cables of 35-50mm Ø



10500

### 10700

- Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping.
- Adjustable cutting depth to prevent damage to the conductors.
- High grade wear resistant polyamide construction - light and strong.
- Spare cutting blade in the handle.
- Working range: Round multicore cables of 50-70mm Ø



10700

### 20030

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for flat twin and earth cables.
- Automatic cable size adjustment for convenience.
- Working Range 0,75 – 0,25 mm<sup>2</sup>



20030

### 20050

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for solid & stranded wires.
- Automatic wire size adjustment for convenience.
- Integrated wire cutter up to 2,5 mm<sup>2</sup>
- Working Range 0,2 – 6 mm<sup>2</sup>



20050

### 20060

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for solid & stranded wires.
- Automatic wire size adjustment for convenience.
- Integrated wire cutter up to 2,5 mm<sup>2</sup>
- Working Range 0,5 – 6 mm<sup>2</sup>



20060

### 20090

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for larger diameter wire and 3-core PVC flex.
- Automatic cable size adjustment for convenience.
- Working Range 6 - 16 mm<sup>2</sup>



20090

### 20100

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed soft grip handles for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for round, solid or stranded cored wire.
- Automatic cable size adjustment for convenience.
- Working Range 0.2 - 6 mm<sup>2</sup>



20100

### 20300

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for stripping Round standard, PUR Halogen - Free Cables, Highly Flexible TPE-U-Cables, PUR-Cables, PUR / PVC Cables, PVC Cables, Multi-Stranded Cables, Shielded and Non-Shielded Cables
- Working Range 4.4 – 7 mm Ø



20300

### 20310

- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for stripping Round standard, PUR Halogen - Free Cables, Highly Flexible TPE-U-Cables, PUR-Cables, PUR / PVC Cables, PVC Cables, Multi-Stranded Cables, Shielded and Non-Shielded Cables.
- Working Range 3.2 – 4.4 mm Ø



20310

### 20450



- Fibreglass-reinforced polyamide construction for high strength and light weight.
- Ergonomically designed for fatigue free, repetitive stripping.
- Stripping length scale for consistent results.
- Designed for stripping difficult insulations, e.g. PMMA fibre optic cables with PE sheath, PVC, rubber, silicon and TPE.
- Working Range 0,5 – 4 mm<sup>2</sup>



20450

### 30010

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all common coaxial cables.
- Also suitable for stripping 3-core flex.
- Working Range 4,8 – 7,5 mm Ø



30010

### 30100

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of Coaxial cable, Tv-Coax, RG 58 / RG 59, PVC-Flex 3 x 0,75mm<sup>2</sup>.
- Two blade pairs at the top of the handle with a Titanium-Nitride coating (TIN) to achieve longer life, faster cutting and less wear.
- Working Range 4.8 – 7.5mm Ø



30100

### 30120

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all common round cables.
- Working Range 8 – 13 mm Ø



30120

### 30140

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all common flat and oval cables.
- Working Range up to 12mm wide



30140

### 30155

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of round cables.
- Pre-set precision stripping blades for damage free conductor stripping.
- Retractable trimming knife blade for convenience
- Titanium –Nitride coated blades for increased durability
- Cable Stripping 8 – 13 mm Ø
- Wire Stripping 0,2 – 4 mm<sup>2</sup>



30155

### 30160

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of datacomms cables.
- Pre-set precision stripping blades for damage free conductor stripping.
- Cable Stripping 5 - 15 mm Ø
- Wire Stripping 0,2 – 4 mm<sup>2</sup>



30160

### 30180

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all standard energy and security cables; double shielded solar cables, shortcircuit and grounding-proof, flame retardant, halogen free cables.
- Working range: Cables of 7.0mm Ø.



30180

### 30190

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all standard energy and security cables; Double shielded solar cables, short circuit and grounding-proof, flame retardant and halogen free cables.
- Working range: Cables of 7.5mm - 9.5mm Ø.



30190

### 30200

- Suitable for stripping all standard energy and security cables: Double shielded solar cables, short circuit and grounding-proof, flame retardant and halogen free cables.
- Working range: Cables of 11mm - 13mm Ø.



30200

### 30400

- Razor sharp, stripping blades for fast, precise and damage free stripping of industrial cables, specifically those used predominantly in the electrical industry and building installation
- Two blade pairs at the top of the handle with a Titanium-Nitride coating (TIN) to achieve longer life, faster cutting and less wear.
- Cable Stripping 8 - 15 mm Ø
- Wire Stripping 1.5 – 2.5mm<sup>2</sup>



30400



### 30500

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of PVC-insulated data cables with thin insulation. Strips the outer insulation and the foil sheathing with one tool easily and quickly.
- Working range: cables of 4.5mm - 10.0mm Ø



30500

### 30600

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of all common coaxial cables.
- Tv-Coax, RG 58 / RG 59, PVC-Flex 3 x 0,75mm<sup>2</sup>
- Visible 20mm length scales
- Cutting blades on both ends of the tool are marked with 1 and 2 for the correct order of use
- Working Range 4,8 – 7,5 mm Ø



30600

### 30700

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of fibre optic cables e.g DAC (Direct Access Cable)
- Working range: Cables of 5.9mm Ø



30700

### 30900

- Razor sharp, preset stripping blades for fast, precise and damage free stripping of round (4-15mm Ø) cables (including data communications cable, coaxial cable and round multicore cables) and flat multicore cables (Max 15mm Width).
- Additional blade included for a longitudinal cut.
- 2 stripping notches with length stop for stripping conductors.
- The removable length stop is suitable for left and right hand use and can be stored in the tool handle.
- Working range: Round cables 4-15 mm Ø. Flat cables max. 15 mm width e.g. YDY, NYM-J.



30900

|        | Item Description                              | EAN No        | Commodity code | Carton Qty |
|--------|-----------------------------------------------|---------------|----------------|------------|
| T10160 | Jokari Cable Knife No 16                      | 4011391101609 | 82119200       | 18         |
| T10270 | Jokari Cable Knife No 27                      | 4011391102705 | 82119200       | 18         |
| T10271 | Jokari Cable Knife No 271S                    | 4011391102712 | 82119200       | 18         |
| T10280 | Jokari Cable Knife No 28H                     | 4011391102804 | 82119200       | 18         |
| T10282 | Jokari Cable Knife No 28H                     | 4011391102828 | 82119200       | 18         |
| T10283 | Jokari Cable Knife Economy                    | 4011391102835 | 82119200       | 18         |
| T10350 | Jokari Cable Knife Secura No. 35              | 4011391103504 | 82119200       | 12         |
| T10500 | Jokari Cable Knife Secura No. 50              | 4011391105003 | 82119200       | 12         |
| T10700 | Jokari Cable Knife No. 70 Standard            | 4011391107007 | 82119200       | 8          |
| T20030 | Jokari Flat Cable Stripper                    | 4011391200302 | 82032090       | 12         |
| T20050 | Jokari Single Core Stripper No 4              | 4011391200500 | 82032090       | 8          |
| T20060 | Jokari Wire Stripper 0.5-6.0mm                | 4011391200609 | 82032090       | 12         |
| T20090 | Jokari Auto Wire Stripper No 6                | 4011391200906 | 82032090       | 12         |
| T20100 | Jokari Secura Auto Wire Stripper              | 4011391201002 | 82032090       | 8          |
| 20300  | Jokari Sensor Special Auto Wire Stripper      | 4011391203006 | 82032090       | 5          |
| T20310 | Jokari Sensor Mini Special Auto Wire Stripper | 4011391203105 | 82032090       | 5          |
| T20450 | Jokari Auto Wire Stripper                     | 4011391205406 | 82032090       | 6          |
| T29030 | Pair of spare blades for T20030               | 5013969020113 | 82032000       | 1          |
| T30010 | Jokari Coaxial Cable Stripper                 | 4011391300101 | 82032090       | 18         |
| T30100 | Jokari Top Coxial Cable Stripper              | 4011391301009 | 82032090       | 18         |
| T30120 | Jokari Cable Stripper No 12                   | 4011391301207 | 82032090       | 18         |
| T30140 | Jokari Flat Cable Striper No 14               | 4011391301405 | 82032090       | 18         |
| T30155 | Jokari Cable Stripper No 15                   | 4011391301559 | 82032090       | 18         |
| T30160 | Jokari Data Cable Stripper                    | 4011391301603 | 82032090       | 18         |
| T30180 | Jokari SE-Strip Cable Stripper                | 4011391301801 | 82032000       | 18         |
| T30190 | Jokari SE-Strip Cable Stripper                | 4011391301900 | 82032000       | 18         |
| T30200 | Jokari SE-Strip Cable Stripper                | 4011391302006 | 82032000       | 18         |
| T30400 | Jokari Uni-Plus Cable Stripper                | 4011391304000 | 82032090       | 12         |
| T30500 | Jokari No.1-Cat Cable Stripper                | 4011391305007 | 82032000       | 18         |
| T30600 | Jokari Secura No1 Coaxial Cable Stripper      | 4011391306004 | 82032090       | 18         |
| T30700 | Jokari Fibre-Strip DC Cable Stripper          | 4011391307001 | 82032000       | 18         |
| T30900 | Jokari Allrounder Cable Stripper              | 4011391309005 | 82032000       | 12         |

|                                    |                                                                   |
|------------------------------------|-------------------------------------------------------------------|
| Technical product information      |                                                                   |
| Standards compliance               | None applicable                                                   |
| User health and safety information | None applicable                                                   |
| RoHS/WEEE                          | This product range does not fall within the scope of RoHS or WEEE |

|                      |                                                                                                                                                                                                |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| compliance           | regulations                                                                                                                                                                                    |
| Material safety data | None applicable                                                                                                                                                                                |
| Warranty             | Jokari Tools are guaranteed for 2 years against imperfect materials or workmanship, except blades and knives<br>Normal wear and tear or damage caused through inappropriate use is not covered |
| Country of origin    | Germany                                                                                                                                                                                        |

## Dimensional details

|        | Product only |          |           |              | Product on primary packaging |          |           |                |
|--------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| Item   | Width mm     | Depth mm | Height mm | Net weight g | Width mm                     | Depth mm | Height mm | Gross weight g |
| T10160 | 132          | 29       | 35        | 75           | 258                          | 81       | 36        | 93             |
| T10270 | 132          | 29       | 35        | 75           | 258                          | 81       | 36        | 93             |
| T10271 | 138          | 38       | 35        | 58           | 258                          | 81       | 38        | 77             |
| T10280 | 170          | 29       | 35        | 85           | 258                          | 81       | 36        | 100            |
| T10282 | 177          | 29       | 22        | 83           | 256                          | 82       | 30        | 103            |
| T10283 | 170          | 29       | 35        | 75           | 250                          | 85       | 36        | 90             |
| T10350 | 138          | 38       | 35        | 58           | 258                          | 81       | 38        | 77             |
| T10500 | 138          | 38       | 35        | 58           | 258                          | 81       | 38        | 77             |
| T10700 | 180          | 38       | 70        | 158          | 258                          | 90       | 38        | 164            |
| T20030 | 166          | 102      | 28        | 124          | 258                          | 81       | 29        | 143            |
| T20050 | 165          | 104      | 27        | 91           | 258                          | 142      | 35        | 119            |
| T20060 | 180          | 105      | 25        | 157          | 258                          | 100      | 27        | 176            |
| T20090 | 166          | 102      | 28        | 125          | 258                          | 81       | 29        | 141            |
| T20100 | 160          | 145      | 25        | 154          | 232                          | 141      | 27        | 181            |
| 20300  | 161          | 112      | 25        | 122          | 240                          | 104      | 72        | 222            |
| T20310 | 161          | 112      | 25        | 122          | 240                          | 104      | 72        | 222            |
| T20450 | 140          | 125      | 25        | 96           | 213                          | 117      | 27        | 121            |
| T29030 | 12           | 4        | 3         | 1            | 40                           | 75       | 3         | 3              |
| T30010 | 100          | 18       | 18        | 22           | 258                          | 81       | 30        | 40             |
| T30100 | 106          | 32       | 20        | 21           | 257                          | 82       | 30        | 42             |
| T30120 | 124          | 35       | 25        | 50           | 258                          | 81       | 30        | 68             |
| T30140 | 124          | 35       | 25        | 49           | 258                          | 81       | 30        | 66             |
| T30155 | 124          | 35       | 25        | 47           | 258                          | 81       | 30        | 64             |
| T30160 | 124          | 35       | 25        | 45           | 258                          | 81       | 30        | 62             |
| T30180 | 100          | 18       | 18        | 22           | 258                          | 81       | 30        | 40             |

|        |     |    |    |    |     |    |    |    |
|--------|-----|----|----|----|-----|----|----|----|
| T30190 | 100 | 18 | 18 | 22 | 258 | 81 | 30 | 40 |
| T30200 | 100 | 18 | 18 | 22 | 258 | 81 | 30 | 40 |
| T30400 | 132 | 35 | 27 | 46 | 255 | 82 | 28 | 65 |
| T30500 | 100 | 18 | 18 | 22 | 258 | 81 | 30 | 40 |
| T30600 | 99  | 21 | 19 | 25 | 270 | 82 | 28 | 44 |
| T30700 | 100 | 18 | 18 | 22 | 258 | 81 | 30 | 40 |
| T30900 | 106 | 32 | 20 | 21 | 257 | 82 | 30 | 42 |

| Item   | Shelf box (secondary packaging) |          |           |                | Euro Pallet data<br>Wi x Hi |                     |
|--------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
|        | Width mm                        | Depth mm | Height mm | Gross weight g | No of cartons on base       | Number of rows high |
| T10160 | 215                             | 320      | 115       | 1900           |                             |                     |
| T10270 | 215                             | 320      | 115       | 1900           |                             |                     |
| T10271 | 215                             | 320      | 115       | 1550           |                             |                     |
| T10280 | 215                             | 320      | 115       | 2000           |                             |                     |
| T10282 | 215                             | 320      | 115       | 2050           |                             |                     |
| T10283 | 215                             | 320      | 104       | 1900           |                             |                     |
| T10350 | 215                             | 320      | 115       | 1550           |                             |                     |
| T10500 | 215                             | 320      | 115       | 1550           |                             |                     |
| T10700 | 215                             | 320      | 115       | 1550           |                             |                     |
| T20030 | 215                             | 320      | 115       | 1950           |                             |                     |
| T20050 | 215                             | 320      | 145       | 1160           |                             |                     |
| T20060 | 215                             | 320      | 157       | 2320           |                             |                     |
| T20090 | 215                             | 320      | 115       | 1900           |                             |                     |
| T20100 | 215                             | 320      | 115       | 1650           |                             |                     |
| 20300  | 215                             | 320      | 115       | 1315           |                             |                     |
| T20310 | 215                             | 320      | 115       | 1315           |                             |                     |
| T20450 | 215                             | 320      | 104       | 950            |                             |                     |
| T29030 | -                               | -        | -         | -              |                             |                     |
| T30010 | 215                             | 320      | 125       | 920            |                             |                     |
| T30100 | 215                             | 320      | 125       | 950            |                             |                     |
| T30120 | 215                             | 320      | 125       | 1450           |                             |                     |
| T30140 | 215                             | 320      | 125       | 1400           |                             |                     |
| T30155 | 215                             | 320      | 125       | 1360           |                             |                     |
| T30160 | 215                             | 320      | 125       | 1300           |                             |                     |
| T30180 | 215                             | 320      | 125       | 920            |                             |                     |

|        |     |     |     |      |  |  |
|--------|-----|-----|-----|------|--|--|
| T30190 | 215 | 320 | 125 | 920  |  |  |
| T30200 | 215 | 320 | 125 | 920  |  |  |
| T30400 | 215 | 320 | 125 | 990  |  |  |
| T30500 | 215 | 320 | 125 | 920  |  |  |
| T30600 | 215 | 320 | 125 | 1000 |  |  |
| T30700 | 215 | 320 | 125 | 920  |  |  |
| T30900 | 215 | 320 | 125 | 920  |  |  |

## Packaging waste details

| Primary Packaging |           |         |        |              | Secondary packaging |     |        |     |
|-------------------|-----------|---------|--------|--------------|---------------------|-----|--------|-----|
| Item              | Plastic g | Use     | Card g | Use          | Plastic g           | Use | Card g | Use |
| T10160            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10270            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10271            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10280            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10282            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10283            | 15        | Blister | No     | Backing Card |                     |     | 202    | Box |
| T10350            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10500            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T10700            | 11        | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T20030            | 7         | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T20050            | 12        | Blister | 16     | Backing Card |                     |     | 202    | Box |
| T20060            | 10        | Blister | 11     | Backing Card |                     |     | 202    | Box |
| T20090            | 7         | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T20100            | 11        | Blister | 16     | Backing Card |                     |     | 202    | Box |
| 20300             | 55        | Blister | 25     | Backing Card |                     |     | 202    | Box |
| T20310            | 55        | Blister | 25     | Backing Card |                     |     | 202    | Box |
| T20450            | no        | Blister | 25     | Backing Card |                     |     | 202    | Box |
| T29030            | 1         | Bag     | -      | -            |                     |     | -      | -   |
| T20450            | no        | Blister | 25     | Backing Card |                     |     | 202    | Box |
| T30010            | 8         | Blister | 9      | Backing Card |                     |     | 202    | Box |
| T30100            | 10        | Blister | 12     | Backing Card |                     |     | 202    | Box |
| T30120            | 8         | Blister | 9      | Backing Card |                     |     | 202    | Box |



|        |    |         |    |              |  |  |     |     |
|--------|----|---------|----|--------------|--|--|-----|-----|
| T30140 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30155 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30160 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30180 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30190 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30200 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30400 | 9  | Blister | 10 | Backing Card |  |  | 202 | Box |
| T30500 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30600 | 9  | Blister | 10 | Backing Card |  |  | 202 | Box |
| T30700 | 8  | Blister | 9  | Backing Card |  |  | 202 | Box |
| T30900 | 10 | Blister | 12 | Backing Card |  |  | 202 | Box |