

(1,00 mm) .0394"

ISS1, CC09, T1M SERIES

DISCRETE WIRE COMPONENTS & TOOLING

SPECIFICATIONS

For complete specifications see www.samtec.com?ISS1 or www.samtec.com?CC09

TOOLING



- Hand tool:
CAT-HT-309-2830-12
- Clamp for mounting
hand tool to work table:
CAT-HT-MNT-01



- Mini Applicator:
CAT-MA-309-2830-FR-01



TYPE

ISS1

= Body, Loose

NO. OF POSITIONS

–02, –03, –05,
–07, –10, –15, –20
(Standard sizes)



Insulator Material:
Nylon

TYPE

01

PLATING

CC09R

= Contact, Full Reel
(30,000 Parts per Reel)

CC09M


= Mini Reel
(5,000 Parts per Reel)

–GF

= 3μ" (0,07 μm) Gold,
50μ" (1,27 μm) Ni
on contact and tail

–T

= Tin



Contact Material:
Phosphor Bronze

SPECIFICATIONS

For complete specifications see www.samtec.com?T1M

Insulator Material:

Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Weld Tab: Phosphor Bronze

Plating: Au or Sn over

50μ" (1,27 μm) Ni

Operating Temp Range:

–55°C to +85°C

Current Rating:

3.3 A per pin

(1 pin powered)

Voltage Rating:

250 VAC/353 VDC

RoHS Compliant: Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



Note: Some lengths, styles
and options are non-standard,
non-returnable.

T1M

NO. OF POSITIONS

PLATING OPTION

S

SMT TYPE

OPTION

TR

Mates with:
S1SS

–02, –03,
–05, –07,
–10, –15, –20
(Standard sizes)

–GF

= 3μ" (0,07 μm) Gold,
50μ" (1,27 μm) Ni on
contact and tail

–T

= Tin

–RA

= Right

Angle

–V


= Vertical

–K


= (4,00 mm)
.157" DIA
Polyimide
Film Pick &
Place Pad
(–V only)

–TR

= Tape &
Reel



–V



–RA

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685