



## 3-in-1 Printer...Labeling, Bar Code and Heat Shrink Tube Identification

The three-in-one industrial printer solves all your labeling needs at a price anyone can afford. The K-Sun LABELShop® BEE3® is perfect for plant, laboratory, facility, office, electrical, warehouse, aviation, home and general identification requirements.

**Works as hard as a Bee!**

*K-Sun LABELShop® BEE3®  
 Is Available In Many Kit Combinations.*



### Printer Features & Functions

- 3 Year FREE Printer Warranty
- Automatic Tape & Heat Shrink Tube Cutter
- Keyboard: 67 Key QWERTY-Compatible Keyboard
- Transparent Tape Cover: Instantly Reveals Tape Color, Size and Remaining Tape, Easy to Change
- LCD Display: 12 Characters, 2-Lines Dot Matrix Standard LCD
- LCD Light Adjustment: 5 Dark to Light Settings
- Print Preview: Shows Label Design and Type Style
- Print Technology: High Durability Thermal Transfer
- Print Resolution: 180 DPI
- Print Speed: All Tapes Print 6mm Per Second or 2.36" Per Second
- Print Density: 3 Dark to Light Settings
- Power: Runs on Batteries- 6AA, AC Power Adapter-115-240V That Complies With California Energy Reduction Requirements & DC Auto & Truck Adapter-12V
- Power Management: Automatic Power Off
- Portability: Hand-Held or Desktop Operation. Built-in Frame Handle and (optional) Nylon Wrist Strap for Enhanced Portability and Protection.
- Printer Dimensions: 7.4" (wide) x 2.3" (high) x 8.8" (deep)
- Printer Weight: 1.23 Lbs.
- Printer Construction: High Impact Plastic with (optional) Rubber Base Guard

### Print Functions

- 6 Bar Code Formats: Code 39, Code 128, ITF, UPC-A, UPC-E, CODABAR
- Cable Label Function: "Quick Key" Speeds Design of Wire and Cable Labels
- Horizontal and Vertical Functions
- 14 Fonts, Bitmap Fonts Installed For Print Characters
- Symbols: 1,028 Special Industrial, Medical, Safety, Office, Home and General Symbols, Punctuation, Math, Arrows and More.
- Font Sizes: 6 point to 26 point Depending on Type Style and Tape Width
- Font Functions: Bitmap Smoothing Function
- Font Styles: Bold, Italic, Shadow, Outline, Shadow+Outline
- Lines of Text: 1 to 4 Lines of Text Depending on Tape Width
- Text Alignment: Left, Center, Right
- Tape Feed and Cut Function Key for Manual Advance
- Back Space and Delete Functions
- Frames: 75 Professional & Decorative
- Print Length: 15", 90 Characters
- Memory Storage: 4 Files
- Euro/Latin Characters: "Quick Key" for easy Entry of European/Latin Language Characters
- Language Prompts: English/Spanish

### Tape and Heat Shrink Tube Supplies

- Tape Selection: 60 Industrial Tapes and 5 Heat Shrink Tube Materials
- Two-in-One Tape: Flexible Polyester Base for Wire and Cable Wrap. Polyester Provides Durability and Permanent Adhesive Strength for Flat Surfaces Too. Solves Two Requirements With One Tape.
- Tape Width Selection: 5-Widths- 1/6" (4mm), 1/4" (6mm), 3/8" (9mm), 1/2" (12mm), 3/4" (18mm)
- Tape complies with ANSI/TIA/EIA-606-A Standards
- Heat Shrink Tube Selection: Polyolefin Heat Shrink Tube Material in 1/8" and 3/16" Widths, Three Color Combinations
- Tape Complies With ANSI/TIA/EIA-606-A Standards

### Environmental and Safety

- Printer Runs on Safe 6.5V DC Power
- Conforms to FCC Class B Standards
- RoHS Directive: Parts Within RoHS Requirements and Standards
- Non-PVC Parts
- Low Battery Warning
- Overheat Detection and Power Shut Off
- Auto Text Storage When Power Out
- Automatic Temperature Sensor
- Battery Reversed Alarm
- Circuit Breaker
- LSAD Adapter: Meets All Requirements for California Energy Commission's Minimum Efficiency and No-Load Energy Reduction Standards
- International AC Power Adapters also available

*12V-DC Auto & Truck Adapter  
 Makes The K-Sun LABELShop®  
 BEE3® Even More Portable and  
 Affordable, Saving on Batteries  
 During Field Operations*





