



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	UPDATE CAP WIDTH	20NOV2019	G,F	S.M


D



C




B



A

Recommended PCB LAYOUT




PRODUCT SPECIFICATION:
1,Current Rating: 2.0AMP
2,Contact Resistance: 20mΩ Max
3,Withstand Voltage: 500V AC
4,Insulation Resistance: 1000MΩ Min
5,Operation Temperature: -40℃ to +105℃

6,Recommend Soldering Process
Reflow Soldering 260
7, Packaging: Tap & Reel with CAP


Material:
HOUSING: HIGH TEMPERATURE PLASTIC, UL94V-0, BK
CONTACT: COPPER ALLOY

FINISH: GOLD FLASH ALL OVER NICKEL



PN:2271007-2

15	20	2271007-2
12	24	2271007-1
POS	NO.OF PINS	PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GEORGE FU 20NOV2019	TE Connectivity					
DIMENSIONS: mm		CHK GEORGE FU 20NOV2019						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD SHI MING 20NOV2019	NAME AMOMODU,REC HDR,2.00PITCH DOU ROW,SMT -					
		PRODUCT SPEC 108-137777						
		APPLICATION SPEC -						
		MATERIAL -	FINISH -	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=2271007	RESTRICTED TO -
		CUSTOMER DRAWING				SCALE 1:1	SHEET 1 of 1	REV B

D

C

B

A