

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0210390231](#)  
**Status:** **Active - Custom**  
**Overview:**  
**Description:** 1.00mm (.039") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 8 Circuits, 0.127m (5.00") Length

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**  
Product Family Cable  
Series [21039](#)  
Comments Contacts on the same side, Type A  
Geographic Area Americas  
Overview Premo-Flex™  
Product Name Premo-Flex™ FFC Jumper

**Physical**  
Cable Length 0.127m (5.00")  
Circuits (Loaded) 8  
Packaging Type Bag  
Pitch - Term. Interface (in) 0.039 In  
Pitch - Term. Interface (mm) 1.00 mm  
Temperature Range - Operating -40°C to +80°C  
Wire Size AWG N/A  
Wire/Cable Type Flat Flex Cable

**Electrical**  
Current - Maximum 1.3A  
Voltage - Maximum 30V

**Material Info**

**Reference - Drawing Numbers**  
Sales Drawing SD-21039-001



Series image - Reference only

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
Not Reviewed  
**Halogen-Free**  
**Status**  
**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**  
Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

Duration at Max. 30  
Process Temperature (seconds)  
Max. Cycles at Max. 1  
Process Temperature  
Process Temperature 250 max. C

**Search Parts in this Series**  
[21039 Series](#)

**Use With**  
Any 1.00mm (.039") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION