






LOOPBACK CONN. P/N	LOOPBACK BODY COLOR
106052-0010	BEIGE
106052-0080	BLACK



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DUST CAPS ARE NOT SHOWN, BUT INCLUDED.
3. FIBER TYPE - MM 50/125µm.

4. MAXIMUM INSERTION LOSS PER CONNECTOR
(TWO MATED PAIRS):
AT 850nm: 2.0dB.
AT 1310nm: 2.0dB.

5. LABEL IS PRINTED WITH "50µm" AND "2dB" AND PLACED
ON THE BACK SIDE OF THE CONNECTOR AS SHOWN.

ENTER DESCRIPTION
EC NO: MF2007-0793
DRWN: IGUMIN 2007/07/09
CHKD: 2007/07/09
APPR: IGUMIN 2007/07/09
REV

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY DATE
IGUMIN 2007/06/29

CHECKED BY DATE

APPROVED BY DATE
IGUMIN 2007/06/29

MATERIAL NO.
SEE TABLE

SIZE
B

SCALE
2:1

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
LC LOOPBACK
MM 50/125UM

MOLEX INCORPORATED

DOCUMENT NO.
SD-106052-0010

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION