


**Accessories**  
**CB 540/7.5 BLACK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

|            |                                                               |
|------------|---------------------------------------------------------------|
| Type       | CB 540/7.5 BLACK                                              |
| Order No.  | <a href="#">7940006073</a>                                    |
| Version    | Cable ties, Height x width: 540 x 7.8 mm, Polyamide 66, 540 N |
| GTIN (EAN) | 4032248520305                                                 |
| Qty.       | 100 pc(s).                                                    |

## Accessories

### CB 540/7.5 BLACK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 7.8 mm | Width (inches)  | 0.307 inch |
| Height     | 540 mm | Height (inches) | 21.26 inch |
| Depth      | 1.9 mm | Depth (inches)  | 0.075 inch |
| Net weight | 7.14 g |                 |            |

### Installation materials

|                                   |        |                                   |              |
|-----------------------------------|--------|-----------------------------------|--------------|
| Cable diameter, max.              | 158 mm | Material                          | Polyamide 66 |
| Operating temperature range, max. | 85 °C  | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 540 N  | UL 94 flammability rating         | V-2          |

### Classifications

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0   | EC000046    |
| eClass 9.0  | 27-14-07-02 | eClass 9.1 | 27-14-07-02 |
| eClass 10.0 | 27-14-07-02 | UNSPSC     | 30-21-18-01 |

### Approvals

Approvals



ROHS Conform

### Downloads

|                                             |                                       |
|---------------------------------------------|---------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">DE PI830000160627_002</a> |
| Engineering Data                            | <a href="#">EPLAN_WSCAD</a>           |

**Data sheet****Accessories  
CB 540/7.5 BLACK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**