

Pneumatic crimping tool - ZAP 100 - 1203259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pneumatic crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross section 4 - 10 mm²

Why buy this product

- ✓ These crimping pliers are pneumatic tools for ferrules with a cross section range of 0.25 to 10 mm²

Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 330 (CL2-2011)
GTIN	 4 017918 018146
Custom tariff number	84678900
Country of origin	GERMANY

Technical data

General

Length (b)	190 mm
Min. AWG, flexible, multi-strand	8
AWG max., flexible, multi-strand	12
Pressure range	4 hPa ... 6 hPa
Air consumption per compression	0.2 l
Weight	0.45 kg
Compression	trapezoidal

Classifications

eclass

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	17130101

Pneumatic crimping tool - ZAP 100 - 1203259

Classifications

eclass

eCl@ss 7.0	17130101
------------	----------

etim

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186

unspsc

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518