





Loose Part No.	1117 ST. S	1117	1116 ST. S	1116	1202 ST. S
Material Thickness/ Type	0.032" (0.81mm) Pre-plated Brass	0.032" (0.81mm) Pre-plated Brass	0.032" (0.81mm) Pre-plated Brass	0.032" (0.81mm) Pre-plated Brass	0.032" (0.81mm) Pre-plated Brass
Standard Finish	Pre-Tinned Brass	Pre-Tinned Brass	Pre-Tinned Brass	Pre-Tinned Brass	Pre-Tinned Brass
Screw Type	Stainless Steel Binding Head 1/4" (6.35mm) x 6-32	No Screw	Stainless Steel Binding Head 1/4" (6.35mm) x 6-32	No Screw	Stainless Steel Binding Head 1/4" (6.35mm) x 6-32
Screw Position	Inserted & Down	N/A	Inserted & Down	N/A	Inserted, Staked & Backed Out
Wire Stop	No	No	Yes	Yes	Yes



Typical PCB Mounting Configuration



Loose Part No.	1030
Material Thickness/ Type	0.032" (0.81mm) Brass
Screw Type	Stainless Steel Binding Head 5/16" (7.92mm) x 6-32
Screw Position	Inserted, Staked and Backed-Out
Standard Finish	100% Matt Tin over Copper



Note: Hidden Surfaces Not Shown to Maintain Illustration Clarity

For exact finish specifications and available special finishes, see Finish Table (page 91).