

LA1KN22

CONTACTOR+RELAY AUX CONTACT 575VAC 10A



List Price \$14.20 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	10A
Inductive Amperes (AC3)	10A
Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR43364 Class: 321102 - CE Marked
Contact Configuration	2 N.O./2 N.C.
Marketing Trade Name	TeSys
Maximum Voltage Rating	600VAC
Mounting Type	Clip-on (Front)
Terminal Type	Screw Clamp
Type	TeSys K
Weight	0.10 Pounds

Notes:

Block of 4 contacts cannot be used with LP4K or LP5K contactors.

Shipping and Ordering

Category	22341 - Contactors, IEC, Accessories, D, K & F-Line
Discount Schedule	I12
GTIN	00785901883289
Package Quantity	1
Weight	0.08 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	ID

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.