



Date	Rev.	Description




Model No.	POS.1	POS.2	POS.3
1MS4	ON	OFF	MOM
Term. Comm.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

SCALE: 3 : 2

TOLERANCE

0.00 mm $\pm$ 0.25mm

0.0 mm $\pm$ 0.40mm

ANGULAR : $\pm$ 0.254 mm

FILE NAME : 1MSP0245

RATING :

R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)

Q : 2Amps @250VAC

5Amps @120 VAC or 28 VDC

SPECIFICATIONS

MECHANICAL LIFE: 40,000 make-and-break cycles.

CONTACT RESISTANCE: 10m Ω max. initial @ 2-4VDC
100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000M Ω min.

DIELECTRIC STRENGTH: 1,000 V RMS@sea level.

OPERATING TEMPERATURE: -30 $^{\circ}$ C to 85 $^{\circ}$ C.

MATERIALS

CASE: Dially phthalate (DAP) (UL94v-0).

ACTUATOR: Brass,chrome plated.

BUSHING: Brass,nickel plated.

HOUSING: Stainless Steel.

TERMINAL/CONTACT: Silver or gold plated.

DCC. NO.
A4 DRAWING NO.

MATERIAL	GOLDSUN ELECTRONICS CO., LTD.			
	JAMECO NO.	317261	GOLDSUN NO.	1MS5T1B1M1QE
DRWN: Kiki Chen	Description	MINIATURE TOGGLE SWITCHES		Rev. 1
VERIFY PEOPLE: Ada Zheng , Ivy Lan	UNIT: mm	SCALE: 3:2	SHEET 1 OF 1	CAS No: ERN No: