







RECOMMENDED
CABLE STRIPPING DIM'S

REV.	DATE	ECR NO.	DESCRIPTION
NC	06/23/10	XXXXXX	INITIAL RELEASE



1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
						DRAWN	M.ZHANG	06/23/10									
						CHECKED				PART DESCRIPTION TNC CRIMP JACK – 75 OHM (FOR RG–59/U CABLE)							
						ISSUED											
						SHEET		1 OF 1		PART NO. 122125							
					CAD FILE		C:/CONNEX/122125.DWG		DWG. NO.		122125.DWG	REV.	NC	SIZE	A	SCALE	NA
5	FERRULE	BRASS	NICKEL	1													
4	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1													
3	INSULATOR	DELRI	NATURAL	1													
2	BODY	BRASS	NICKEL	1													
1	HOUSING	BRASS	NICKEL	1													
DESCRIPTION					MATERIAL		FINISH		QTY								