

CC2000, TYPE 12



INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997
cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997

NEMA/EMAC Type 12
IEC 60529, IP55
DIN 40050

Standard Product

Catalog Number	AxBxC mm/in.	Body Style	Usable Area D x E mm/in.	Depth F mm/in.	Cutout Size	Weight (lb.)
CC376129	375 x 615 x 290 14.76 x 24.21 x 11.42	Solid	300 x 540 11.81 x 21.26	—	60	32
CC466129	465 x 615 x 290 18.46 x 24.21 x 11.42	Solid	390 x 540 15.35 x 21.26	—	60	35
CC616129	615 x 615 x 290 24.21 x 24.21 x 11.42	Solid	540 x 540 21.26 x 21.26	—	60	39
CC616151	615 x 615 x 518 24.21 x 24.21 x 21.57	Solid	540 x 540 21.26 x 21.26	—	80	72
CC376518	375 x 465 x 180 14.76 x 18.46 x 7.09	Hinged	300 x 390 11.81 x 15.35	127 5.00	60	22
CC466618	465 x 465 x 180 18.46 x 18.46 x 7.09	Hinged	390 x 390 15.35 x 15.35	127 5.00	60	24

Cutout is for flange coupling only. Other components can be used if they have the same hole size.

APPLICATION

CC2000 is the perfect solution for housing flat and touch screen HMI devices in applications where accessories are unnecessary, and simplicity and stylish attractiveness are important. This easy-to-use enclosure is ideal for housing simple devices that contain their own controls.


SPECIFICATIONS

- Extruded Type 6063 aluminum top and sides provide a quality appearance and internal flexibility
- Body is available hinged or solid
- Rear doors can be hinged on either the right or left side
- Integral mounting system has extruded screw channels to facilitate easy component installation
- Each size accommodates a range of flat screen HMI devices
- Oil-resistant gasket attached with oil-resistant adhesive
- High thermal conductivity for superior heat dissipation


FINISH

Enclosure vertical components are clear anodized aluminum; horizontal components are painted RAL 7043 gray aluminum. Aluminum front plates and rear doors have a clear anodized brushed finish.



BULLETIN: CC2



Solid Enclosure



Hinged Enclosure




Pendant Cutout

FRONT PLATE



Front Plates are available in 14 gauge aluminum with clear anodized brushed finish.
Hoffman can provide pre-configured front plates to meet your specific requirements. Contact your local Hoffman Sales Representative for more information.

BULLETIN: CC2



Catalog Number	Plate Size D x E mm/in.	M x N mm/in.	Fits Enclosure mm/in.	Weight (lb.)
C2FP3155	314 x 554 12.36 x 21.81	540 x 300 21.26 x 11.81	375 x 615 x 290 14.76 x 24.21 x 11.42	3.0
C2FP4055	404 x 554 15.90 x 21.81	540 x 390 21.26 x 15.35	465 x 615 x 290 18.46 x 24.21 x 11.42	3.8
C2FP5555	554 x 554 21.81 x 21.81	540 x 540 21.26 x 21.26	615 x 615 x 518/290 24.21 x 24.21 x 21.57/11.42	5.4
C2FP3140	314 x 404 12.36 x 15.90	390 x 300 15.35 x 11.81	375 x 465 x 180 14.76 x 18.46 x 7.09	2.2
C2FP4040	404 x 404 15.90 x 15.90	390 x 390 15.35 x 15.35	465 x 465 x 180 18.46 x 18.46 x 7.09	2.8