

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050032](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite Wet Location 30W 12V Spotlight with Screw Release Guard, Battery Clips
16/2 SOOW, Overall Length 15.24m (50.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
UL	E30252
General	
Product Family	Portable Lighting
Series	130105
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Outlet	None
Overview	Specialty Lighting
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862534

Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	127.00mm (5.000")
Length	228.60mm (9.000")
Material - Guard	#10 Gauge Vinyl Coated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical	
Bulb Type	Quartz Halogen
Cord Type - Secondary	16/2 SOOW
Lamp Type	PAR36
Lamp Wattage - Maximum	30W
Lumens	300
On/Off Switch	No
Voltage (Fixture) - Maximum	12V

Material Info	
Engineering Number	1606



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130105](#) Series