


Backlit with Self Adhesive Legends



- Backlit for Low Light Applications
- Waterproof Silicone Rubber
- Audible, Tactile Contacts
- Low Contact Resistance
- Optional RFI/EMI Shielding
- 3,000,000 Operations per Button

[illegible]

SCHEMATIC AND TRUTH TABLE



LED Color	Forward Voltage			Resistor (OHMS)	Typ. Current Consumption (With 5V Pwr. Supply)	
	Min.	Typ.	Max.		3 x 4	4 x 4
Red	-	1.95	2.40	43	155mA	205mA
Yellow/Green	-	1.95	2.40	43	155mA	205mA
Green	1.50	-	2.40	43	155mA	205mA
Orange	-	1.95	2.40	43	155mA	205mA

SPECIFICATIONS

Rating Criteria

Rating at 24 Vdc: - 10 milliamps resistive (max.)

Contact Bounce: 4 milliseconds maximum at make; 10 milliseconds, at break

Contact Resistance: 10 ohms maximum

Life Expectancy: 3 million operations/button

Insulation Resistance: >1,000 megohms

Operating Features

Pre-Travel: .030 inches minimum

Operating Force: 20 ± 4 ounces

Humidity: 0 to 98% (no condensation)

Materials and Finishes

Terminal Pins: Copper alloy CDA 725

PC Board: FR-4 glass cloth epoxy

Dome Retainer/Rear Seal Sheet: Polyester

Mounting Studs: Phosphor bronze

Optional Hex Nut: Stainless steel, passivated

Optional EMI Shield: Aluminum foil

Keypad: Silicone rubber

SELF-ADHESIVE LEGEND SHEETS

Each 8.5" x 11" legend sheet contains commonly used symbols, terms, alpha characters and 0-9 in helvetica bold type. Self-adhesive legends are clear urethane on a chrome mylar base. Adhesive is silicone/acrylic. Legends can be purchased in the following ways:

1. Entire legend sheets: Part numbers 84AC5012-1, -2, -3 OR -4.
2. Individual legends: Part numbers 84AC5012-0001, -0002 etc. (Individual legend pins are for groups of 10 legends each)
3. See Grayhill drawing 84AC5012-X for detailed information on available legends, sizes and fonts.

ORDERING INFORMATION

