




FEATURES:

- Ideal for providing jumper wires between small components.

MATERIALS:

Conn: 1st End - Minipincer® Test Clip

Material: Beryllium copper contact.

Finish: Gold plated.

Insulation: Nylon

Wire: 20 AWG, 41 x 36 t.c. PVC insulated, 2.2 (.087) O.D.

Marking: "POMONA 5419-XX-*)"

Conn: 2nd End – Same as first

RATINGS:

Operating Temperature: +80°C. (+176°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC Max.

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 5419-XX-*

XX – Cable Lengths, Standard Lengths: 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524).

*= Color, -0 Black, -2 Red

Ordering Example: 5419-60-2 Indicates 60" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5419-48-2](#) [5419-48-0](#) [5419-12-0](#) [5419-36-0](#) [5419-12-2](#) [5419-36-2](#) [5419-18-0](#) [5419-18-2](#) [5419-8-0](#) [5419-24-0](#)
[5419-24-2](#) [5419-60-2](#) [5419-60-0](#)