

WhisperGreen CFM Premium Ceiling Fan

[FIND ANOTHER MODEL ▶](#)

Model number: FV-08VKML2


[Print this](#) | [Share this](#)

Product no longer available for purchase.

WhisperGreen CFM Premium Ceiling Mounted Continuous and Spot Ventilation Fan with SmartAction Motion Sensor and Light
Online Order Assistance

- Track your order
- Print your invoice
- Read our shipping FAQs
- Register your product

Accessories

- Find accessories for your product

Contact Us

- Phone
- Email
- Mail
- International Support

Tech Specifications

Static Pressure (in inches w.g.)	0.1 0.25
Air Volume (CFM)	84, 71, 59, 51, 40, 32 CFM @ .25 w.g. 80, 70, 60, 50, 40, 30 CFM @ .1w.g.
Noise (sones)	.1 w.g. 0.3 @ 80 CFM <0.3 @ 70, 60, 50, 40, 30 CFM .25 w.g.N/A @ 84, 71, 59, 51, 40, 32 CFM
Power Consumption (Watts)	.25 w.g. 17.6 @ 84 CFM 15.1 @ 71 CFM 12.7 @ 59 CFM 11.2 @ 51 CFM 9.8 @ 40 CFM 8.5 @ 32 CFM .1 w.g.12.6 @ 80 CFM 9.6 @ 70 CFM 7.8 @ 60 CFM 6.8 @ 50 CFM 6.2 @ 40 CFM 5.3 @ 30 CFM
Energy Efficiency (CFM's/Watt)	.25 w.g. 4.8 @ 84 CFM 4.8 @ 71 CFM 4.7 @ 59 CFM 4.7 @ 51 CFM 4.5 @ 40 CFM 4.4 @ 32 CFM .1 w.g.6.3 @ 80 CFM 7.5 @ 70 CFM 7.9 @ 60 CFM 7.8 @ 50 CFM 7.3 @ 40 CFM 6.4 @ 30 CFM
Speed (RPM)	.25 w.g. 975 @ 84 CFM 958 @ 71 CFM 941 @ 59 CFM 925 @ 51 CFM 905 @ 40 CFM 879 @ 32 CFM .1 w.g.807 @ 80 CFM 723 @ 70 CFM 675 @ 60 CFM 661 @ 50 CFM 645 @ 40 CFM 611 @ 30 CFM
Current (Amps)	.25 w.g. 0.12 @ 84 CFM 0.11 @ 71 CFM 0.09 @ 59 CFM 0.08 @ 51 CFM 0.07 @ 40 CFM 0.06 @ 32 CFM .1 w.g.0.09 @ 80 CFM 0.07 @ 70 CFM 0.06 @ 60 CFM 0.05 @ 50 CFM 0.04 @ 40 CFM 0.04 @ 30 CFM
Power Rating (V/Hz)	120/60
Motor Type	DC
Type of Motor Bearing	Ball
Thermal Fuse Protection	Yes
Blower Wheel Type	Sirocco
Duct Diameter (inches)	4"
Mounting Opening (inches sq.)	107/8"
Grille Size (inches sq.)	13"
SmartAction™ Motion Sensor	Yes
High/Low Delay Timer	Yes
CustomVent™ Variable Speed Control	Yes
SmartFlow™ Optimum CFM Technology	Yes
Lamp Watts	2 x 18 watts
Lamp Color Rendering Index	84
Color Temperature (Kelvin)	3,500
Rated Life (hours)	10,000
Lamp Model #	FDS18E35/4 ¹
Night Light Lamp Watts	4
Washington State VI AQ Code	Yes
California Title 24 Compliant	Yes
Mfg in ISO 9001 Certified Facility	Yes
Energy Star Qualified	Yes
Gross Weight (lbs.)	16.3
UL tub/Shower Enclosure	Yes
Dimensions (H x W x D)	13.39" x 14.37" x 16.93"
Weight	16.1 lbs

1. Lamp contains mercury. Dispose according to local, state and Federal laws.