



## Large Cabinet Racks Economizer



## ***Design Features***

Welded Frame: 14-gauge steel vertical rails. 16-gauge steel top and bottom. Uniquely designed, 16-gauge steel rail supports. Furnished complete with removable sides, rear door and one pair of panel mounting rails.

Panel Mounting Rails: 12-gauge steel. Fully adjustable, tapped #10-32 in front on E.I.A. universal spacing. (Use #7346 screws - order separately) Separate .28 diameter holes provided for mounting accessories.

Side Panel: 20-gauge steel. Removable from outside for easy access.

Bottom: Pierced for RC-7758 casters, and with one 9.56 square hole and four 1.11 knock outs for cable access.

1200# Equipment load capacity.

## Bonus Features

## *Finishes*




Sand Texture (S), Royal Blue Texture (RB), and Black Texture (BT) are standard.  
Available in other Bud textured finishes at no extra cost.

| Economizer Racks with 19" Panel Width |             |          |                |             |          |                   |                     |                    |                    |                         |               |
|---------------------------------------|-------------|----------|----------------|-------------|----------|-------------------|---------------------|--------------------|--------------------|-------------------------|---------------|
| Non-Ventilated                        |             |          | Ventilated     |             |          | Panel Space<br>PS | Outside Height<br>A | Outside Width<br>B | Outside Depth<br>C | Clear Inside Depth<br>D | Weight (Lbs.) |
| Catalog Number                        | Accessories | Drawings | Catalog Number | Accessories | Drawings |                   |                     |                    |                    |                         |               |

|          |  |  |          |     |     |        |        |        |        |        |     |
|----------|--|--|----------|-----|-----|--------|--------|--------|--------|--------|-----|
| ER-16502 |  |  | ER-16602 |     |     | 42.00" | 47.31" | 22.00" | 18.50" | 17.00" | 110 |
| ER-16503 |  |  | ER-16603 |     |     | 52.50" | 57.81" | 22.00" | 18.50" | 17.00" | 124 |
| ER-16504 |  |  | ER-16604 |     |     | 61.25" | 66.56" | 22.00" | 18.50" | 17.00" | 139 |
| ER-16505 |  |  | ER-16605 |     |     | 70.00" | 75.31" | 22.00" | 18.50" | 17.00" | 151 |
| ER-16506 |  |  | ER-16606 |     |     | 78.75" | 84.06" | 22.00" | 18.50" | 17.00" | 163 |
| ER-16511 |  |  | N/A      | N/A | N/A | 21.00" | 25.31" | 22.00" | 25.50" | 24.00" | 94  |
| ER-16512 |  |  | ER-16612 |     |     | 42.00" | 47.31" | 22.00" | 25.50" | 24.00" | 128 |
| ER-16513 |  |  | ER-16613 |     |     | 52.50" | 57.81" | 22.00" | 25.50" | 24.00" | 145 |
| ER-16514 |  |  | ER-16614 |     |     | 61.25" | 66.56" | 22.00" | 25.50" | 24.00" | 162 |
| ER-16515 |  |  | ER-16615 |     |     | 70.00" | 75.31" | 22.00" | 25.50" | 24.00" | 175 |
| ER-16516 |  |  | ER-16616 |     |     | 78.75" | 84.06" | 22.00" | 25.50" | 24.00" | 189 |
| ER-16521 |  |  | N/A      | N/A | N/A | 21.00" | 25.31" | 22.00" | 30.75" | 29.25" | 109 |
| ER-16522 |  |  | ER-16622 |     |     | 42.00" | 47.31" | 22.00" | 30.75" | 29.25" | 143 |
| ER-16523 |  |  | ER-16623 |     |     | 52.50" | 57.81" | 22.00" | 30.75" | 29.25" | 160 |
| ER-16524 |  |  | ER-16624 |     |     | 61.25" | 66.56" | 22.00" | 30.75" | 29.25" | 180 |
| ER-16525 |  |  | ER-16625 |     |     | 70.00" | 75.31" | 22.00" | 30.75" | 29.25" | 194 |
| ER-16526 |  |  | ER-16626 |     |     | 78.75" | 84.06" | 22.00" | 30.75" | 29.25" | 209 |

- NOTES:**
- ① PANEL MOUNTING RAILS TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING AND ARE FULLY ADJUSTABLE.
  - ② MOUNTING HOLES PIERCED IN BASE FOR #RC-7758 CASTERS.
  - ③ LOAD RATING: 1200 LBS. MAX.
- ☒ (2) SETS OF (10) HOODED LOUVERS CENTERED ON EACH SIDE.  
☐ (2) SETS OF (15) HOODED LOUVERS CENTERED ON EACH SIDE.  
☐ (4) SETS OF (10) HOODED LOUVERS ON EACH SIDE.  
☐ (4) SETS OF (15) HOODED LOUVERS ON EACH SIDE.

MOUNTING PROVISIONS FOR OPTIONAL FAN.




**MATERIAL:**

|                                           |              |
|-------------------------------------------|--------------|
| SIDES AND REAR DOOR                       | 20 GA. STEEL |
| REAR DOOR STIFFENER                       | 18 GA. STEEL |
| TOP, BOTTOM, RAIL SUPPORTS AND DOOR STOPS | 16 GA. STEEL |
| VERTICAL RAILS                            | 14 GA. STEEL |
| PANEL MOUNTING RAILS                      | 12 GA. STEEL |

**FINISH:**

|                                     |                    |
|-------------------------------------|--------------------|
| FRAME ASSEMBLY, SIDES AND REAR DOOR | SAND TEXTURE       |
|                                     | ROYAL BLUE TEXTURE |
|                                     | BLACK TEXTURE      |
| PANEL MOUNTING RAILS AND DOOR STOPS | SMOOTH BLACK       |



|                                              |               |        |        |        |        |        | OPTIONAL ACCESSORIES      |                          |
|----------------------------------------------|---------------|--------|--------|--------|--------|--------|---------------------------|--------------------------|
| PART NO.                                     | PANEL SPACE A | B      | C      | D      | E      | F      | PANEL MTG. RAILS PART NO. | PLEXIGLAS DOORS PART NO. |
| ER-16602 <input checked="" type="checkbox"/> | 42.000        | 47.312 | 18.500 | 17.000 | —      | 38.562 | PMR-9450                  | V-9063-A                 |
| ER-16603 <input type="checkbox"/>            | 52.500        | 57.812 |        |        | —      | 49.062 | PMR-9451                  | V-9064-A                 |
| ER-16604 <input type="checkbox"/>            | 61.250        | 66.562 |        |        | 27.531 | 57.812 | PMR-9452                  | V-9065-A                 |
| ER-16605 <input type="checkbox"/>            | 70.000        | 75.312 |        |        | 31.906 | 66.562 | PMR-9453                  | V-9066-A                 |
| ER-16606 <input type="checkbox"/>            | 78.750        | 84.062 | 18.500 | 17.000 | 36.281 | 75.312 | PMR-9454                  | V-9067-A                 |
| ER-16612 <input type="checkbox"/>            | 42.000        | 47.312 | 25.500 | 24.000 | —      | 38.562 | PMR-9450                  | V-9063-A                 |
| ER-16613 <input type="checkbox"/>            | 52.500        | 57.812 |        |        | —      | 49.062 | PMR-9451                  | V-9064-A                 |
| ER-16614 <input type="checkbox"/>            | 61.250        | 66.562 |        |        | 27.531 | 57.812 | PMR-9452                  | V-9065-A                 |
| ER-16615 <input type="checkbox"/>            | 70.000        | 75.312 |        |        | 31.906 | 66.562 | PMR-9453                  | V-9066-A                 |
| ER-16616 <input type="checkbox"/>            | 78.750        | 84.062 | 25.500 | 24.000 | 36.281 | 75.312 | PMR-9454                  | V-9067-A                 |
| ER-16622 <input type="checkbox"/>            | 42.000        | 47.312 | 30.750 | 29.250 | —      | 38.562 | PMR-9450                  | V-9063-A                 |
| ER-16623 <input type="checkbox"/>            | 52.500        | 57.812 |        |        | —      | 49.062 | PMR-9451                  | V-9064-A                 |
| ER-16624 <input type="checkbox"/>            | 61.250        | 66.562 |        |        | 27.531 | 57.812 | PMR-9452                  | V-9065-A                 |
| ER-16625 <input type="checkbox"/>            | 70.000        | 75.312 |        |        | 31.906 | 66.562 | PMR-9453                  | V-9066-A                 |
| ER-16626 <input type="checkbox"/>            | 78.750        | 84.062 | 30.750 | 29.250 | 36.281 | 75.312 | PMR-9454                  | V-9067-A                 |