





LEAD FREE

PC BOARD MOUNTING DIMENSIONS



- 1 MATERIAL:
 ③ SHELL - STAINLESS STEEL.
 CONTACTS - COPPER ALLOY.
 HOUSING - UL 94V-0 RATED, THERMOPLASTIC, FOR COLOR SEE TABLE.
- 2 PLATING:
 CONTACTS - 0.076um MINIMUM GOLD OVER 0.76um MINIMUM PALLADIUM-NICKEL
 ON MATING AREA, 3.8um MINIMUM MATTE TIN ON SOLDER TAILS,
 BOTH OVER 1.27um MINIMUM NICKEL.
 CONTACT ALTERNATE PLATING: 0.76um MINIMUM GOLD ON MATING
 AREA, 3.80um MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
 1.27um MINIMUM NICKEL.
 SHELL - 2~5um MINIMUM BRIGHT TIN.
- 3 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57mm.

NATURAL	5787834-2
BLACK	5787834-1
HOUSING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28MAY2004 Ivanov Wang CHK 28MAY2004 Steven Yao		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.1 2 PLC ± 0.05 3 PLC ± 0.013 4 PLC ± - ANGLES ± -		NAME Takinori Sasaki PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL 		FINISH 		WEIGHT - A2 00779 C-5787834	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1
				REV A4	