

T9A Series



- ### U.L. Contact Ratings for KRPA

Ruggedly constructed relay offered with silver contacts, code "Y", rated 5 amps; and silver-cadmium oxide contacts, code "G" rated 10 amps. Contact arrangements are available up through 3 form (3PDT). Expected life exceeds 100,000 operations at rated load. Mechanical life is 10 million operations, minimum. Enclosed in a clear dust cover. U.L. recognized under file E22575. Low cost version of the KRP relay.

KRPA-N Series has an indicator lamp wired in parallel with its coil, making this model ideal for voltage or current monitoring applications. Silver-cadmium oxide contacts are rated 10 amps. KRPA-N specifications are identical to those of other models in the KRPA series.

19AS — Mounting and Termination Code

Diagram illustrating the mounting and termination code for the 19AS connector. Dimensions are provided in inches (in) and millimeters (mm).

Key dimensions and tolerances:

- 0.140 Max. (3.56)
- 0.250 Max. (6.35)
- 0.100 (2.54)
- 0.300 (7.62)
- 0.061 ± 0.006 Lsk. (2.06 ± 0.15)
- 0.043 ± 0.003 Dia. (1.09 ± 0.08)
- 0.600 (15.24)
- 0.500 (12.7)
- 0.150 (3.81)
- 0.550 (13.97)
- 0.500 (12.7)
- 0.150 (3.81)
- 0.750 (19.05)
- 0.300 (7.62)
- 0.100 (2.54)
- 0.061 ± 0.006 Lsk. (2.06 ± 0.15)
- 0.043 ± 0.003 Dia. (1.09 ± 0.08)
- 0.150 (3.81)
- 0.750 (19.05)
- 0.300 (7.62)
- 0.100 (2.54)
- 0.061 ± 0.006 Lsk. (2.06 ± 0.15)
- 0.043 ± 0.003 Dia. (1.09 ± 0.08)

1 Form C
(Unused Terminals Are Not Present)

T9A Series are low cost, printed circuit board or panel mount relays. Up to 30 A switching in SPST and 20 A in SPDT arrangements. Silver-cadmium oxide contacts in 1 Form A (SPST-NO) and 1 Form C (SPDT). Available in unsealed, plastic dust cover (T9AP) or immersion cleanable, sealed plastic case (T9AS). UL Class F insulation system standard. Well suited for various industrial, commercial and residential applications.

Stock No.	Mr.'s Type	Volts (DC)	Termination	Contacts	EACH		
					1-24	25-49	50-Up
886-2101	T9AS1D12-12	12	P.C. Mount	SPST-NO	3.10	2.74	2.48
886-2102	T9AS1D12-12	12	P.C. Mount	SPDT	2.66	2.29	2.09
886-2103	T9AS1D12-24	24	P.C. Mount	SPST-NO	3.10	2.74	2.48
886-2104	T9AS5D12-24	24	P.C. Mount	SPDT	2.70	2.38	2.19
886-2106	T9AS1D12-18	18	P.C. Mount	SPST-NO	2.70	2.38	2.19
886-2107	T9AP5D52-12	12	Flange Mount, Q.C.	SPDT	3.82	3.37	3.06
886-2108	T9AP5D52-24	24	Flange Mount, Q.C.	SPDT	3.81	3.38	3.06
886-2109	T9AS1D22-12	12	P.C. Mount, Q.C.	SPST-NO	3.35	2.97	2.69
886-2110	T9AS1D22-24	24	P.C. Mount, Q.C.	SPST-NO	2.95	2.66	2.43
886-2111	T9AS5D22-12	12	P.C. Mount, Q.C.	SPDT	2.95	2.66	2.43
886-2112	T9AS5D22-24	24	P.C. Mount, Q.C.	SPDT	2.95	2.61	2.36