

Chip Aluminium Electrolytic Capacitors

SMC-11

(1 Flap FL16/10) 16 Werte / 290 Stück

Chip – Alu-elkos

Type/Fab.: CB/TEAPO, MVK/NCC oder Alternative

Toleranz: $\pm 20\%$

Temperatur: -40 bis +105°C

Werte-Mengen Verteilung:

0,10uF/50V	25x	2,2uF/50V	25x	6,8uF/25V	10x	22uF/25V	10x
0,22uF/50V	25x	3,3uF/50V	15x	10uF/16V	20x	33uF/25V	10x
0,47uF/50V	25x	4,7uF/25V	25x	10uF/50V	20x	47uF/16V	10x
1,0uF/50V	25x	4,7uF/50V	25x	22uF/ 6V	10x	100uF/ 6V	10x