




1. MATERIAL
- ① HOUSING : HIGH TEMP, THERMO-PLASTIC, UL94V-0, BLACK
 - ② CONTACT : COPPER ALLOY
FINISH : Au PL. AT CONTACT AREA ON OVERALL OVER Ni UNDER PL. 0.00127 MIN.
 - ③ SOLDER BALL : Sn/Ag/Cu FOR LEAD FREE PRODUCT
 - ④ CAP : HIGH TEMP. THERMO-PLASTIC, UL94V-0, BLACK
- △ INDICATED DATE CODE ON THE HSG

A-A (SCALE 2:1)
(SOCKET ASSY IS NOT SECTIONEND)

0.76 um MIN	1554116-3
0.38 um MIN	1554116-2
Au AT CONTACT AREA	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.TOKUNAGA 17MAY2010	TE Connectivity		
DIMENSIONS: mm		CHK H.TAGUCHI 17MAY2010			
		APVD T.NAKASHIMA 17MAY2010	NAME		
		PRODUCT SPEC	SOCKET ASSY LGA1356-2		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-78496	SIZE		
0 PLC ±		APPLICATION SPEC	CAGE CODE		
1 PLC ±		114-5432	DRAWING NO		
2 PLC ± ±0.5		WEIGHT 13.4 g	RESTRICTED TO		
3 PLC ± ±3		CUSTOMER DRAWING	SCALE 1:1		
4 PLC ±			SHEET 1 OF 4		
ANGLES ±			REV C		
FINISH -					

1554116-2, -3 : AS SHOWN

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D

C

B


A

D

C

B

A



1554116-2, -3 : AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.3
1 PLC	± 0.3
2 PLC	± 0.3
3 PLC	± 0.3
4 PLC	± 0.3
ANGLES	± 3°
FINISH	-

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SOCKET ASSY
LGA1356-2

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=1554116

—

SCALE


NTS

SHEET

2 of 4


REV

C




1554116

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
DIMENSIONS: mm		CHK —			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME	
		PRODUCT SPEC —		SOCKET ASSY LGA1356-2	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		APPLICATION SPEC —		SIZE	
MATERIAL		WEIGHT —		CAGE CODE	DRAWING NO
FINISH		CUSTOMER DRAWING		A2 00779	RESTRICTED TO —
				SCALE	REV
				NTS	3 OF 4



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
		CHK			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm				SOCKET ASSY	
		0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		LGA1356-2	
MATERIAL		FINISH		SIZE	CAGE CODE
				A2	00779
				DRAWING NO	
				RESTRICTED TO	
		WEIGHT		C-1554116	
CUSTOMER DRAWING				SCALE	NTS
				SHEET	4 of 4
				REV	C