

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0711095332
Status: Obsolete
Description: 0.762mm (.030") Pitch HiSpec™ Slot 2 Edge Card Connector - Double-Sided Dual Read-Out, Vertical, with Snap-in 3.56mm (.140") Metal Pin, 2.92mm (.115") PC Tail Length, 330 Circuits

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	71109
Component Type	Edgecard to PCB
Product Name	Edge Card, HiSpec™

Physical

(p)ower-(s)ignal Configuration	330s - 0p
Circuits (Loaded)	330
Circuits (maximum)	330
Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	N/A
Material - Plating Mating	Gold
Material - Plating Termination	90/10 Tin Lead, Tin-Lead
Material - Resin	High Temperature Thermoplastic
PC Tail Length	2.92mm (.115")
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm (.094")
Packaging Type	Tray
Pitch - Mating Interface	0.76mm (.030")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	5.080µm (200µ")
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V

Solder Process Data

Lead-free Process Capability	SMC & Wave Capable (TH only)
Process Temperature max. C	260

Material Info

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71109Series](#)