



**Part Number: 500072-0981**

0.50mm Pitch FFC/FPC Connector, Right Angle, SMT, Easy-On™, BackFlip™, Top Contact Style, 98 Circuits, Gold Contact Plating



Series image - Reference only

Status:	<b>OBsolete</b>
Replacement:	<a href="#">5000720989</a>
Series:	500072
Category:	FFC/FPC Connectors

**Product Environmental Compliance**

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC:

Low-Halogen Status: Not Reviewed

**Part Detail**
**General**

Status	<b>Obsolete</b>
Category	FFC/FPC Connectors
Series	<a href="#">500072</a>
Product Name	Easy-On™

**Physical**

Circuits (Loaded)	98
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	20
Entry Angle	90° Angle
Mated Height	5.60mm
Material - Metal	Phosphor Bronze
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	FFC/FPC

**Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	0.3A
Voltage - Maximum	100V

**Material Info**

UPC	756054369258
-----	--------------

**Reference - Drawing Numbers**

Product Specification	PS-500072-001
Sales Drawing	SD-500072-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application**
**Tooling**
[Check our list of old tooling that used to be available for this part](#)

