

10 9 8 7 6 5 4 3 2 1

F

E





D

C


B

A

LC CONNECTOR HEAD
(2x)



LABEL
SEE NOTE 6



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DUST CAPS ARE NOT SHOWN, BUT INCLUDED.
3. FIBER TYPE - MM 62.5/125μm.
4. MAXIMUM INSERTION LOSS PER CONNECTOR (TWO MATED PAIRS):
AT 850nm: 2.0dB.
AT 1310nm: 2.0dB.
5. OPERATING TEMPERATURE RANGE: -40° TO +85°C.
6. LABEL IS PRINTED WITH '62.5um' AND '2dB' AND PLACED ON THE BACK SIDE OF THE CONNECTOR AS SHOWN.

ENTER DESCRIPTION EC NO: MF2006-0361 DRAWN: RPACIFICI CHKD: CHKD APPR: LGUMIN REV A	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY RPACIFICI	DATE 2005/11/22	TITLE LC LOOPBACK MM 62.5/125UM		
			4 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX INCORPORATED		
			3 PLACES	± ---	± ---					
			2 PLACES	± ---	± ---					
			1 PLACE	± ---	± ---					
			ANGULAR ±1/2°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. 1060520040		DOCUMENT NO. SD-106052-0040		SHEET NO. 1 OF 01				
		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							