

RoHS Compliant

UC-414

uPCI 3+1xRS232+LPT Printer Port

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description


Universal PCI providing four RS232 serial ports and one LPT port (3 industry standard 9 pin D RS232 ports on the bracket with a another 9 pin D RS232 port on a flylead. The 25pin D LPT port is also available by a flylead. Up to 115,200 data transfer rates and the 64 byte deep transmit and 64 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Includes drivers for all Windows 32 bit and 64 bit Operating Systems, including Windows 7.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Features

- 4 port RS232
- PCI 3.0
- 64 Byte Tx and 64 Byte Rx FIFOs
- Up to 115,200 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



UC-414:
uPCI 3+1xRS232+LPT
Printer Port


Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit & 64 bit Editions
- Windows Server 2008 32 bit & 64 bit Editions
- Windows Vista 32 bit & 64 bit editions
- Windows XP 32 bit & 64 bit editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.




ORDER

Description

uPCI 3+1xRS232+LPT Printer Port

Code

UC-414



uPCI 3+1xRS232+LPT Printer Port

UC-414 Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	4 x RS232 DB9 Connector (9 Pin Male) and LPT port 64 RX FIFO + 64 TX FIFO EIA - RS232 Standard 1 port RS232 on fly lead
Port Settings 	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	115,200 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 Point to Point
Interface 	OS Compatibility BUS	Microsoft Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions DOS Plus Printer Port : null
Approvals 	Industry Approvals Microsoft Approvals	Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit & 64 bit editions Windows Server 2003 32 bit & 64 bit editions
General 	PCB Layers Power Consumption Weight Size	4 300mA @ 5V, 60mA @ 12V 0.098 kgKg 133(l) x 18(w) x 120(h) mm mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities uPCI 3+1xRS232+LPT Printer Port 1 port RS232 on fly lead
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Other PCI Cards: 1xRS232 | 2xRS232 | 4xRS232 | 8xRS232 | 1xRS422/485 | 2xRS422/485 | 4xRS422/485

Other Brainboxes Ranges: PCI Express | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial

+44(0) 151 220 2500 | sales@brainboxes.com | www.brainboxes.com