

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 853708

REVISIONS

POINT OF MEASUREMENT
INSIDE OF RECEPTACLE

-:0.78/.081 DIA.

SECTION A-A

SECTION B-B

- ① NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA AND WIRE BARREL.
- ② GOLD FLASH OVER NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER MATING AREA.
- ③ NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA.

MINI	GOLD 	.012 BRASS	61314-7
↑	GOLD 	↑ PH. BRZ.	↑ -6
	GOLD 	BRASS	-5
	PRE-TIN	PH. BRZ	-4
	—	PH. BRZ.	-3
↓	—	↓ BRASS	↓ -2
MINI	PRE-TIN	.012 BRASS	61314-1
APPLICATOR TYPE	FINISH	MATERIAL	PART NO

		APPLICATOR TYPE	FINISH	SIZE DRASS	61314-1
				MATERIAL	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .015$ ANGLES $\pm$	CONTRACT NO		 AMP INCORPORATED Harrisburg, Pa.		
	DR <i>M. FEHER 11-30-79</i>				
MATERIAL SEE TABLE	CHK <i>D.S. Heide 12/11/79</i>		NAME SOCKET, COMMERCIAL MATE-N-LOK™		
	APPD <i>D. DeLoach 12/12/79</i> APPD				
FINISH SEE TABLE	WIRE RANGE 24-18 AWG.		SIZE B	CODE IDENT NO 00779	DRAWING NO 61314
	INSULATION DIA 100 MAX		SCALE 5-1	SHEET 1 OF 1	