

300A AC Analog Clamp Meter

Rotary Scale with Pointer Lock

Freezes the reading on the display

Features:

- Single function/range switch for easy one-handed operation
- Jaw opens to 1.5" (38mm)
- AC/DC Voltage and Resistance measurement
- Pointer Lock function freezes the reading
- Zero adjust
- Complete with test leads, 1.5V battery, and carrying case



Applications:

- Utility Company maintenance and installation
- Plant Maintenance
- Electrical installation and repair
- Automotive repair and testing
- Appliance insulation testing
- HVAC troubleshooting



Specifications	Range	Accuracy
AC Current	6, 15, 60, 150, 300A	±3.0%FS
AC Voltage	300, 600V	±3.0%FS
DC Voltage	75V	±3.0%FS
Resistance	2kΩ	±3.0% of Scale Length
ACA Frequency Response	50 to 400Hz	
Dimension/Weight	9x2.8x1.5" (230x72x37mm)/14.5oz (416g)	

Ordering Information:

AM300300A AC Analog Clamp Meter
AM300-NISTAM300 with Certificate of Calibration Traceable to NIST.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[AM300](#)