





- 1 WIRE SIZE AND LOGO APPEAR ON OUTSIDE OF WIRE BARREL.
- 2 RETENTION CLIP: PHOSPHOR BRONZE PER QQ-B-750.
PIN CONTACT: COPPER PER QQ-C-576.
- 3 PIN CONTACT: $0.76\mu\text{m}$ [.000030] MIN GOLD PER MIL-G-45204 ON CONTACT MATING END, GOLD FLASH ON REMAINDER, ALL OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL PER QQ-N-390.
RETENTION CLIP: $2.54\mu\text{m}$ [.000100] MIN NICKEL PER QQ-N-290.
- 4 PIN CONTACT: $5.08\mu\text{m}$ [.000200] MIN SILVER PER QQ-S-365 ON CONTACT MATING END, $1.27\mu\text{m}$ [.000050] MIN SILVER ON REMAINDER, ALL OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL PER QQ-N-290.
RETENTION CLIP: $2.54\mu\text{m}$ [.000100] MIN NICKEL PER QQ-N-290.



OBSOLETE	3	12.32 [.485]	-	28.52 [1.123]	DETAIL X	213845-8
OBSOLETE	4	12.32 [.485]	-	28.52 [1.123]	DETAIL X	213845-7
	3	12.32 [.485]	32.84 [1.293]	28.52 [1.123]	-	213845-6
	4	12.32 [.485]	32.84 [1.293]	28.52 [1.123]	-	213845-5
	3	10.16 [.400]	-	26.37 [1.038]	DETAIL X	213845-4
	4	10.16 [.400]	-	26.37 [1.038]	DETAIL X	213845-3
	3	10.16 [.400]	30.68 [1.208]	26.37 [1.038]	-	213845-2
	4	10.16 [.400]	30.68 [1.208]	26.37 [1.038]	-	213845-1
FINISH		C	B	A	LOOSE PIECE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G.LENKER 30 JUL 96	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 05 AUG 96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV G.STEINHÄUER 06 AUG 96	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	PIN CONTACT ASSEMBLY 14-12 AWG, .125 POWERBAND	
MATERIAL		APPLICATION SPEC		
FINISH SEE TABLE		WEIGHT	SIZE A1	CAGE CODE 00779
2		CUSTOMER DRAWING	DRAWING NO 213845	RESTRICTED TO -
		SCALE 10:1	SHEET 1	OF 1
			REV B2	