

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191990011](#)
Status: **Active**
Description: Butt - Window Splice for 10-12 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Splices
Series [19199](#)
Comments Mil Spec M7928/5-5
Mil-Spec M7928/5-5
Product Name Butt - Window

Physical
Barrel Type Closed
Insulation Nylon (PA)
Material - Metal Copper
Packaging Type Bag
Temperature Range - Operating -55°C to +105°C
Wire Insulation Diameter 5.79mm (.228") max
Wire Size AWG 10, 12
Wire Size mm² 3.30 - 5.00

Electrical
Voltage - Maximum 300V

Material Info
Old Part Number WC-842

Reference - Drawing Numbers
Sales Drawing CD81000



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status

China RoHS



Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19199Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION