

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating:Flash Gold

Contact Material: Brass





Current Rating : 1A AC,DC

Contact Resistance: 20mΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



P.C.B LAYOUT

NUMBER OF POSITIONS	DIMENSION	
	A	B
06	2.54	18.31
08	3.81	19.58
10	5.08	20.85
12	6.35	22.12
14	7.62	23.39
16	8.89	24.66
20	11.42	27.20
26	15.24	31.01
30	17.78	33.55
34	20.32	36.09
40	24.13	39.90
50	30.48	46.25
60	36.83	52.60
64	39.37	55.14

UNLESS TOLERANCE		DRAW		Cnc Tech,LLC	
GENERAL	ANGLE	DESIGN	BY		
X. ± 0.30	X.° ± 3.0°	CHECK	BY		
.X ± 0.20	.X° ± 2.0°				
.XX ± 0.15	.XX° ± 1.0°				
.XXX ± 0.08	.XXX ± 0.5°				
SCALE		SHEET	UNIT	Part NO. 3210-XX-001-11-00	
1:1		1/1	MM		
				DRAW NO:	
				REV: A	