




JKL LAMP PART NUMBER	COLOR LCD HIGH OUTPUT WHITE 8800°k RGB	STARTING CIRCUIT VOLTAGE VS (Vrms) @ 0°C	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) AVERAGE
BF3380-24B	x = .285 y = .278	1975	790	5 ± 1	28,000 $\pm 10\%$	40,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

	METRIC	DIMENSIONS ARE IN MILLIMETERS				
	THIRD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED	TITLE			
		1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0	MINIATURE COLD CATHODE FLUORESCENT LAMP			
	DRAWN BY L. WENGSTROM	APPV'D BY J.K.	DATE 8/9/04	SIZE A	FSCM NO. 55335	DRAWING NO. BF3380-24B
	RELEASED	8/9/04	- CAD DRAWING -			
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	SCALE NONE	RELEASED DATE 8/9/04	REVISION DATE	REV. NO.
		MANUAL REVISIONS NOT PERMITTED				SHEET 1 OF 1