


LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-06-012328	31MAY2006	KS	KW



152±2	1064530-2
200±5	1064530-1
LENGTH	PART NUMBER

<u>ELECTRICAL</u> FREQUENCY NOMINAL IMPEDENCE VOLTAGE RATING VSWR (MATED CONNECTORS ONLY) INSULATION RESISTANCE DIELECTRIC WITHSTANDING VOLTAGE		DC — 6 GHz 50 OHMS 250 VOLTS (VRMS MAX) @ SEA LEVEL 1.20:1 MAX @ 2 GHz 1.40:1 MAX @ 6 GHz 1,000 MEGOHMS MIN @ 250VDC 500 VOLTS (VRMS MIN) @ SEA LEVEL			
<u>MECHANICAL</u> CONNECTOR DURABILITY ENVIRONMENTAL TEMPERATURE RATING		100 MATING CYCLES -40°C(-40°F) TO +125°C(257°F)			
PRODUCT SPEC					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM CHK KE WEIDNER APVD KE WEIDNER PRODUCT SPEC APPLICATION SPEC WEIGHT	04MAY2006 04MAY2006 04MAY2006	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 4 PLC ± - ANGLES ± 1°	NAME SSMT RIGHT ANGLE JACK TO JACK CABLE ASSEMBLY			
MATERIAL -	FINISH -	SIZE A2		GAGE CODE 00779	DRAWING NO C-1064530
		RESTRICTED TO -		SCALE 15:1 SHEET 1 OF 1 REV C	
CUSTOMER DRAWING					