



Soberton Inc.

Product Data Sheet

Part No. PB-2410 Non-Washable Type



DIMENSIONS



Type	Unit	PB-2410-1
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~20
Current Consumption	(mA)	< or =15
Sound Output (Min)	(dB)	> or = 86
Resonant Frequency	(Hz)	3400±500
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	3
Dimension	mm	23.5 x H9.5
*Value applying at rated voltage		
*distance for measurement 10cm		

Type	Unit	PB-2410-2
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~20
Current Consumption	(mA)	< or =10
Sound Output (Min)	(dB)	> or = 95
Resonant Frequency	(Hz)	3400±500
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	3
Dimension	mm	23.5 x H9.5
*Value applying at rated voltage		
*distance for measurement 10cm		