



## CIRCUIT BOARD HARDWARE

## LONG NOSE CIRCUIT BOARD SUPPORT (LNCBS)




- Speeds assembly because long nose automatically locates and aligns connector pins with socket
- Installs with no tools
- Board lifts off easily to provide quick access to components
- Materials: Nylon 6/6, RMS-01, Flame Retardant Nylon, RMS-19
- Colour: Natural
- Standard Pack: 1000 per bag




| inches (mm)     |                           |            |
|-----------------|---------------------------|------------|
| Part #<br>Nylon | Part #<br>Flame Retardant | "A"        |
| LNCBS-3-01      | LNCBS-3-19                | 3/16 (4.8) |
| LNCBS-4-01      | LNCBS-4-19                | 1/4 (6.4)  |
| LNCBS-6-01      | LNCBS-6-19                | 3/8 (9.5)  |
| LNCBS-8-01      | LNCBS-8-19                | 1/2 (12.7) |
| LNCBS-10-01     | LNCBS-10-19               | 5/8 (15.9) |
| LNCBS-12-01     | LNCBS-12-19               | 3/4 (19.1) |
| LNCBS-14-01     | LNCBS-14-19               | 7/8 (22.2) |

## CIRCUIT BOARD SUPPORTS ON BASE (CBSB/LCBSB)



- Available without adhesive backing. For new "A" Dim., subtract 1/32" (.8 mm) from Dim. "A" and delete "A" from part number
- Adhesive, RMS-15

| inches (mm)    |              |
|----------------|--------------|
| Part #         | "A"          |
| CBSB-3-01A-RT  | 3/16 (4.8)   |
| CBSB-4-01A-RT  | 1/4 (6.4)    |
| CBSB-6-01A-RT  | 3/8 (9.5)    |
| CBSB-8-01A-RT  | 1/2 (12.7)   |
| CBSB-10-01A-RT | 5/8 (15.9)   |
| CBSB-12-01A-RT | 3/4 (19.1)   |
| CBSB-14-01A-RT | 7/8 (22.2)   |
| CBSB-16-01A-RT | 1 (25.4)     |
| CBSB-18-01A-RT | 1-1/8 (28.6) |



- Material: Nylon 6/6, RMS-01; Flame Retardant Nylon, RMS-19, available by special order
- Colour: Natural
- Standard Pack. 1000 per bag

| inches (mm)     |              |
|-----------------|--------------|
| Part #          | "A"          |
| LCBSB-3-01A-RT  | 3/16 (4.8)   |
| LCBSB-4-01A-RT  | 1/4 (6.4)    |
| LCBSB-6-01A-RT  | 3/8 (9.5)    |
| LCBSB-8-01A-RT  | 1/2 (12.7)   |
| LCBSB-10-01A-RT | 5/8 (15.9)   |
| LCBSB-12-01A-RT | 3/4 (19.1)   |
| LCBSB-14-01A-RT | 7/8 (22.2)   |
| LCBSB-16-01A-RT | 1 (25.4)     |
| LCBSB-18-01A-RT | 1-1/8 (28.6) |

