

- Replacement for 10W halogen bulbs
- Up to 90% energy saving
- Lifetime of 25,000 hrs
- Suitable replacement for bi-pin lamps used for accent lighting, vanity and cabinet lighting.



Order Code 52143

General Data

Lamp Socket G4 Bi Pin
Design Capsule

Geometric Data

Length (mm) 41
Diameter (mm) 13.8
Weight (g) 8

Electric Data

Wattage (W) 1
Wattage Equivalent (W) 10
Voltage (V) 12V DC/AC
Power Factor -
Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 80
Luminous Flux 90° cone (lm) n/a
CRI ≥ 80
CCT (K) 2700
Luminous Intensity (cd) 27
Beam Angle (°) 100

Lifespan


Lifetime (hrs) 25,000
Switching Cycle 40,000

Dimmability No

Energy Efficiency Class A++



ø13.8mm





Order Code

52143

Product Description

LED BI PIN G4 Capsule 1.0W 12V AC/DC 2700K WW 80LM

Technical Packaging Details

Barcode	023942521433
EAN 128	(02)00023942521433(37)10(91)14
EAN 14	50023942521438
Pack Dimensions (HxWxL)	
Pack Weight	TBC
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	145*95*155
Cartons/Pallet	276
Layers/Pallet	6
Units/Pallet	2760

Photometric Diagram

52143

