


Card Edge Connectors

164-0810-E, 164-0820-E, 164-0826-E,
164-0834-E, 164-0840-E, 164-0850-E

KOBICONN

Card Edge Connectors

164-0810-E, 164-0820-E, 164-0826-E, 164-0834-E, 164-0840-E, 164-0850-E



(Strain Relief Sold Separately)

Dimensions: mm (In.)

MECHANICAL SPECIFICATIONS

Insulator:	PBT, glass reinforced
Contact:	Brass
RoHS Compliant	

ELECTRICAL SPECIFICATIONS

Current Rating:	1 Amp
Contact Resistance:	30 mΩ max.
Insulator Resistance:	3000 MΩ min.
Dielectric Withstanding Voltage:	500V AC for 1 min.
Operating Temperature:	-40°C to +105°C
Terminated with 1.27mm pitch flat ribbon cable.	

Part No.	Position	A	B
164-0810-E	10	22.36 (.880)	10.16 (.40)
164-0820-E	20	35.06 (1.380)	22.86 (.90)
164-0826-E	26	42.68 (1.680)	30.48 (1.20)
164-0834-E	34	52.84 (2.080)	40.64 (1.60)
164-0840-E	40	60.46 (2.380)	48.26 (1.90)
164-0850-E	50	73.16 (2.880)	60.96 (2.40)

Tolerance

.X	± 0.3
.XX	± 0.2
.XXX	± 0.1

Unless Otherwise Specified

Connector	Strain Relief
164-0810-E	164-0810-1-E
164-0820-E	164-0820-1-E
164-0826-E	164-0826-1-E
164-0834-E	164-0834-1-E
164-0840-E	164-0840-1-E
164-0850-E	164-0850-1-E

Date Last Revised: 8-10-09

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301069

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[164-0850](#) [164-0826](#) [164-0810-E](#) [164-0820-E](#) [164-0826-E](#) [164-0834-E](#) [164-0840-E](#) [164-0850-E](#)