



Product Data Sheet


Part No. PB-2416 Non-Washable Type

DIMENSIONS

PB-2416



$\phi 23.8 \times H16.0$



Type	Unit	PB-2416-1	PB-2416-2	PB-2416-3
Rated Voltage	(VDC)	12	12	12
Operating Voltage	(VDC)	3~20	3~20	3~20
Current Consumption	(mA)	< or = 8	< or = 8	< or = 10
Sound Output (Min)	(dB)	> or = 85	> or = 85	> or = 90
Resonant Frequency	(Hz)	2800±500	2800±500	2800±500
Operating Temp	(C)	-20~+60	-40~+85	-20~+60
Storage Temp	(C)	-30~+70	-40~+85	-30~+70
Weight	(g)	5	5	5
Dimension	mm	23.8 x H16	23.8 x H16	23.8 x H16

*Value applying at rated voltage

*distance for measurement 30cm