



LOC		DIST		REV		DATE		APPRO	
6	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	
						REV. RDRW, 8 SM PKG PER 0720-0040-93	3-17-93	3-17-93	3-17-93

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed	
16-14HD AWG SOLID OR STRANDED		16-14HD AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
16-14HD AWG SOLID OR STRANDED		NOT APPLICABLE	

1 STAMP AMP 16-14HD* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	170°C MAX
VOLTAGE RATING:	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:	1.04-2.62mm² [2.050-5.180] CIR MILS
SOLID OR STRANDED	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ± ANGLES ±	DR 3-17-93 GL KRUBER CHK 3-17-93 DA PATTERSON APPD 3-17-93 DE MILLER APPD 3-17-93 JL MECKLEY PRODUCT SPEC
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727

100	LOOSE PIECE, BOX	8-34567-1
2500	ON TAPE	2-34567-1
---	LOOSE PIECE	34567
QUANTITY	PACKAGING TYPE	PART NO

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
HEAVY DUTY, SOLISTRAND™

SIZE	CAGE CODE	DRAWING NO
00779	00779	34567
SCALE	8:1	SHEET