


LOC		DIST		REVISIONS			
				ZONE	LTR	DATE	APP
6	14	P					
				A	REVISED PER 0720-0230-93	2/28/94	W. J. O'NEAL

DIMENSIONS LISTED IN mm [INCHES]



Technical drawing of a mechanical part with the following dimensions and tolerances:

- Overall length: 10.74 MAX [.423]
- Overall width: 8.56 MAX [.337]
- Top hole diameter: 1.65 MIN DIA [.065]
- Bottom hole diameter: 0.79 ± 0.05 [.031 ± .002]
- Distance from top hole to bottom hole: 3.96 MIN [.156]

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES— TOLERANCES ON 2 PLG DEC ± . 3 PLG DEC ± . ANGLES ± .	DR 2-23-93 JA BRINKMAN CHK 2-23-93 DA PATTERSON	AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL	APPD 2-23-93 DE MILLER		NAME TERMINAL, SLOTTED RING TONGUE, BUDGET
COPPER PER ASTM B-152 ANNEALED	APPD 2-23-93 JL RECKLEY		
PRODUCT SPEC			
FINISH TIN PLATE 0.00254T.000100J MIN THK PER MIL-T-10727	APPLICATION SPEC - WEIGHT -	SIZE  00779 SCALE 10:1	DRAWING NO  323835 SHEET 1 OF 1

CUSTOMER DRAWING