




TYPE 1.




TYPE 2.




TYPE 3.




TYPE 4.




TYPE 5.




TYPE 6.



TYPE 7.



TYPE 8.



TYPE 9.

PART NO.	DIA. (OR "W") ±.020 [±0.5]	HEIGHT "H" ±.020 [±0.5]	6 X 12 MATRIX KISS CUT PAD PCS/PAD	TYPE	QTY.CTN	
RBS-3R	.50 [12.7]	.23 [5.8]	200	1 (PYRAMID)	5000	
RBS-19	.81 [20.5]	.30 [7.6]	98		2646	
RBS-20	.40 [10.2]	.10 [2.5]	242		5082	
RBS-29	.78 [19.8]	.25 [6.4]	98		2940	
RBS-32R	.50 [12.7]	.12 [3.1]	200		5000	
RBS-1		.14 [3.5]		5000		
RBS-5		.06 [1.6]		5000		
RBS-6		.25 [6.3]		5000		
RBS-11	.62 [15.9]	.40 [10.1]	128	2 (CYLINDRICAL)	2560	
RBS-24	.81 [20.5]	.12 [3.1]	72		2520	
RBS-34	.37 [9.5]		300		6000	
RBS-35		.19 [4.8]	200		5000	
RBS-41	.78 [20.0]	.20 [5.1]	84		3360	
RBS-44	.75 [19.1]	.16 [4.1]	98		2450	
RBS-72	1.24 [31.5]	.10 [2.5]	32		2400	
RBS-2	.44 [11.1]	.20 [5.1]	242		3 (DOMES)	5082
RBS-8	.70 [17.6]	.38 [9.6]	98			2254
RBS-12	.38 [9.6]	.15 [3.8]	72	7200		
RBS-15	.62 [16.0]	.31 [7.9]	128	3200		
RBS-22	.38 [9.6]	.21 [5.4]	300	6000		
RBS-27	.31 [7.9]	.08 [2.2]	450	5400		
RBS-37	.72 [18.3]	.56 [14.2]	100 SEPARATE PARTS	1500		
RBS-39	.75 [19.1]	.07 [1.9]	84	5040		
RBS-40	.25 [6.4]	.06 [1.6]	578	15028		
RBS-30	1.8 [45.7]	.60 [15.8]	100 SEPARATE PARTS	4 (ROUND)	500	
RBS-17	.88 [22.3]	.40 [10.1]	72	5 (ROUND)	1440	
RBS-4	.78 [19.8]	.38 [9.7]	100 SEPARATE PARTS	6 (SQUARE)	5600	
RBS-36	1.00 [25.4]	.18 [4.7]	55		2310	
RBS-18	.50 [12.7]	.14 [3.5]	200	7 (ROUND)	5000	
RBS-33-SD		.15 [3.8]		8 (ROUND-PYRAMID)	5000	
RBS-7	.335 [8.6]	.085 [2.2]	450	9 (DOMES)	5400	
RBS-10	.39 [10]	.12 [3]	288		7200	

NOTES:
1. MATERIAL: POLYURETHANE (RMS-64),
60-70 DUROMETER, SHORE A.
2. STANDARD COLOR: CLEAR AND BLACK:
TO ORDER BLACK ADD "-BK" TO PART NO.
BROWN "-BN", WHITE "-WH", OR GRAY "-GY"
AVAILABLE BY SPECIAL ORDER ONLY.
PART NO. RBS-33-SD AND RBS-10 AVAILABLE IN CLEAR ONLY.
3. ADHESIVE: RUBBER (RMS-68).
4. LIGHTER BUMPER COLORS MAY SHOW SOME DARKENING
OR YELLOWING WHEN NOT STORED IN ORIGINAL UNOPENED CARTON.
*NON STAINING, NON MARRING.
*CRACK RESISTANT.

			TITLE: RICHCO BUMPERS					DWG IN IN [MM]	
			CREATED USING SOLIDWORKS	FILE #: RBS		DWN: SM	APP: DJZ		FINAL
X	SEE CO 200507 FOR CHANGES	SK	03/08/10	SHEET: 1 OF 1		DT: 08/12/04	CHKD: RG		PART #
W	SEE CO 200500 FOR CHANGES	SK	02/22/10	SHEET SIZE: B		RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060	
-	SEE ENGINEERING FOR REV. A-V	-	----					SEE TABLE	
REV.	DESCRIPTION	ENGR.	DATE	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°				PRINT TYPE CA	